
509/509T 1/4"-3"

Bronze Check Valve 125 SWP - 200 WOG † Horizontal Swing • Threaded Ends Conforms to: MSS SP-80



DIMENSIO				
Units	Size	Α	В	Cv
Inches mm	1/4	2.13 54	1.44 37	3.3
Inches mm	3/8	2.13 54	1.44 37	6.0
Inches mm	1/2	2.31 59	1.44 37	10.0
Inches mm	3/4	2.63 67	1.69 43	18.0
Inches mm	1	3.25 83	2.00 51	31.0
Inches mm	1 1/4	3.56 91	2.13 54	54.0
Inches mm	1 1/2	4.00 102	2.38 60	76.0
Inches mm	2	4.75 130	2.81 208	131.0
Inches mm	*2 1/2	6.00 152	3.63 92	192.0
Inches mm	*3	6.88 175	4.19 106	297.0

† Non-Shock

IN EVERY VALVE

The information presented on this sheet is correct at time of publication. Milwaukee Valve reserves the right to change design and/or materials without notice. For our Installation, Operation and Maintenance Manual and the most current product information go to www.milwaukeevalve.com. A State of California Prop 65 **WARNING:** Cancer and Reproductive Harm. For more information visit www.p65warnings.ca.gov.

MATERIAL LIST					
No.	PART	MATERIAL	SPECIFICATION		
1	Body	Bronze	ASTM B62		
2	Сар	Bronze	ASTM B62		
3 La		St. Steel-509	Commercial 1/2" to 2" Incl.		
	Lever	Bronze-509	ASTM B584 2 1/2" and 3"		
		Brass-509T	ASTM B16 1/4" to 2" Incl.		
4 Disc		Duran 500	ASTM B16 1/4" to 3/4"		
	Disc	Brass-509	ASTM B453 1" to 1 1/2"		
		Bronze-509	ASTM B62 2" to 3"		
		PTFE-509T	Commercial		
	Disc Holder	Brass	ASTM B16 1/2" to 3/4"		
	(509T Only)	Bronze	ASTM B62 1" to 3"		
6	Pin	St. Steel	Commercial		
7	Disc Nut	Brass	ASTM B16		
8	Retaining Ring	St. Steel	Commercial		
9	Plug (not shown)	Brass	ASTM B16		
10	Washer (not shown)	Brass	ASTM B16		

Note: Not intended for use in potable water.



BI-42