

## PF2200 Series

# Two-Piece Toilet Vitreous China



### Product Features

- Two-piece vitreous china, available 10", 12", 14" RI
- Gravity fed (1.6gpf/6.0Lpf)
- Continuous integral open rim
- 2" glazed trapway
- 8" x 9" water surface
- Close coupled tank with cover
- Anti-siphon ballcock prevents back-siphoning
- Sanitary bar on all bowls
- Quick connect, 2 bolt tank to bowl installation
- Color matched trip lever
- Available with Fluidmaster upgrade
- Available with RH trip lever
- Available with insulated tank
- Available round front, elongated and ADA
- Seat and supply not included



PF2201WH / PF3212WH

### Codes and Standards

- ADA
- IAPMO/UPC
- ASME A112.19.2
- CSA B45.0
- CSA B45.1

### Technical Information

Fixture is ADA compliant.	<b>ADA</b>
<b>Fixture:</b>	
Configuration	two-piece toilet
Water per flush	1.6 gpf/6.0 lpf
Spud size	N/A
Passageway	2" glazed
Water area	8" X 9"
Water depth from rim	6 1/2"
Seat post hole centers	5 1/2"

### Specified Model

Model	Model Description	Color Finishes
PF2200	Bowl only open rim RF	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF2201	Bowl only open rim EB	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF2203	Bowl only open rim ADA height	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF3212	Tank only 12" RI for 2200 series	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF3312	Tank with Fluidmaster 400A, for 12" RI	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF3210	Tank only 10" RI for 2200 series	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF3214	Tank only 14" RI for 2200 series	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone
PF140934PK	Ballcock assy for PF3212 tank	<input type="radio"/> White <input type="radio"/> Biscuit <input type="radio"/> Bone

Add "R" to tank for RH tank lever (3212 only)  
add "U" to tank for insulated tank (3212 only)




## PF2200 Series

# Two-Piece Toilet Vitreous China



### Product Specification:

The combination toilet shall be made of vitreous china. Toilet shall be 1.6 gpf (6.0 lpf). Toilet shall have 2" (5.1cm) glazed trapway. Toilet shall include color matched trip lever. Toilet shall be less seat and supply. Toilet shall be ADA compliant (PF2203) with 17" high bowl.



	P22200	PF2201	PF2203
A	27 3/4" (705)	29 1/2" (749)	30 1/2" (775)
B	16 1/2" (419)	18 1/2" (470)	18 1/2" (470)
C	14 1/2" (368)	14 1/2" (368)	16 1/2" (419)

### Warranty and Codes:

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO fixtures carry a 1-year limited warranty. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless we agree in writing to do otherwise.

