
# Incandescent

# **Close-to-Ceiling**



Туре -09 -10 -20 -30 P3408

	Finish						
Catalog	Brushed Polished Antique				Dimensions (Inches)		
No.	Nickel	Brass	Bronze	White	Lamping A B		
P3408	-09	-10	-20	-30	1 (m) 60w 7-1/2 4-7/8		



## **Specifications:**

General

- White glass shade
- (3) installed fitter screws to retain glass
- Plated Brushed Nickel (-09), polished brass (-10) and antique bronze (-20) finishes
- Painted White (-30) finish
- Steel construction

### Mounting

- Ceiling mount
- Ceiling pan covers a standard 4" recessed hexagonal outlet box
- Mounting strap for outlet box included
- Keyhole slots for easy mounting

#### Electrical


- Pre-wired
- Requires 90 degree supply wire connections
- Medium base porcelain socket
- 6" of wire supplied

#### Labeling

UL-CUL Damp location listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

#### **Close-To-Ceiling** Fitter **Compact Fluorescent** Energy Star<sup>®</sup> Qualified Туре -09WB P3408 Finish Catalog Brushed **Dimensions (Inches)** Lamping No. Nickel В Α 7-1/4 P3408 -09WB 1 GU-24 13w 4-5/8 (included)



# Electrical

- GU24 base plastic socket
- 6" of wire supplied
- Pre-wired
- Requires 90 degree supply wire connections

### Labeling

cCSAus Damp location listed





• White glass shade

• Steel construction

• Ceiling ctc mount

Mounting

• Energy Star<sup>®</sup> gualified

• (3) installed fitter screws to retain glass

• Plated Brushed Nickel (-09WB) finish

• Ceiling pan covers a standard 4" hexagonal recessed outlet box

• Keyhole slots for easy mounting

• Mounting strap for outlet box included

