

## Single-handle bathroom sink faucet, 1.2 gpm K-77958-4A

#### **Features**

- 5.1" (129 mm) spout reach
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Single pin handle allows for both volume and temperature control
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom
- KOHLER ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

## Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

#### Installation


- For single-hole installation
- Preattached flexible supply lines simplify installation

### **Water Conservation & Rebates**

 This product can help a building earn Water Efficiency points in LEED® Green Building Rating System

## **Recommended Products/Accessories**

K-23726 Drain treatment K-23723 Faucet cleaner



ADA CSA B651

ASME A112.18.1/CSA B125.1

OBC



## Codes/Standards

NSF/ANSI/CAN 61 NSF/ANSI/CAN 372 All applicable US Federal and State material regulations DOE - Energy Policy Act 1992 EPA WaterSense®

California Energy Commission (CEC) ADA ICC/ANSI A117.1 CSA B651 OBC

# KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.


## **Available Colors/Finishes**

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne



## Single-handle bathroom sink faucet, 1.2 gpm K-77958-4A



## **Technical Information**

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Spout:

Spout reach: 5-1/16" (129 mm)

### **Notes**

Install this product according to the installation instructions.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

