


aquatherm greenpipe® - elbow 90°


Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	z	l	D	Weight
	Nom. I.D.	pc	[in]	[in]	[in]	[in]	lb/pc
0112106	3/8"	10	0.63	0.35	0.87	0.96	0.02
0112108	1/2"	10	0.79	0.43	1.00	1.16	0.04
0112110	3/4"	10	0.98	0.53	1.16	1.34	0.06
0112112	1"	5	1.26	0.67	1.38	1.69	0.09
0112114	1.25"	5	1.57	0.83	1.63	2.05	0.16
0112116	1.5"	5	1.97	1.02	1.95	2.68	0.36
0112118	2"	1	2.48	1.28	2.36	3.31	0.61
0112120	2.5"	1	2.95	1.52	2.70	3.94	0.97
0112122	3"	1	3.54	1.81	3.11	4.72	1.76
0112124	3.5"	1	4.33	2.20	3.66	5.79	3.11
0112126	4"	1	4.92	3.01	4.59	6.57	4.33

aquatherm greenpipe® - elbow 90°

Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	z	Weight
	Nom. I.D.		[in]	[in]	lb/pc
0112130	6" -- (SDR 7.4)	1	6.30	5.71	5.74
0112131	6" -- (SDR 11)	1	6.30	5.71	4.32
0112134	8" -- (SDR 7.4)	1	7.87	17.72	25.78
0112135	8" -- (SDR 11)	1	7.87	17.72	17.95
0112138	10" -- (SDR 7.4)	1	9.84	24.61	57.33
0112139	10" -- (SDR 11)	1	9.84	24.61	39.69