

SUBMITTAL COVER SHEET

DDO IECT NAME	
PROJECT NAME	
LOCATION	
ARCHITECT	
ENGINEER	
CONTRACTOR	
REFERENCE	
SUBMITTED BY	DATE

Indoor Unit (IDU): DRAW09F1B	Outdoor Unit (ODU): DRA1U09S1B	Wireless Remote Control
SOURCE	DURASTAR	

#### **PRODUCT FEATURES**

- Wireless Remote Control with "Follow Me" Technology
- Variable Speed Inverter Compressor
- Auto Restart
- Sleep Mode
- Turbo Mode
- 24-Hour Timer Feature
- Quiet operation
- 46°F Freeze Protection
- Low ambient heating down to -13 °F
- Low ambient cooling down to 5 °F
- Included base pan heater
- Refrigerant leak detection
- Anti-corrosive fin coating

CAPACITIES		
Cooling Capacity (BTU/hr)	Rated at 95 °F	9000
	Sensible at 5 °F³	8010
	Minimum	2500
	Maximum	11900
Heating Capacity (BTU/hr)	Rated at 47 °F	10000
	Rated at 5 °F <sup>4</sup>	8300
	Minimum	3400
	Maximum	13000

SYSTEM DATA	
Refrigerant Type	R-410A
Refrigerant Charge (oz.)	38.1
Design Pressure (PSIG)	550/340
Indoor/ Oudoor Coil Coating	Golden Fin Coating

EFFICIENCY DATA		
SEER2	24.0	
EER2	14.7	
HSPF2	11.6	
SEER	24.0	
EER	14.7	
HSPF	12.7	
COP at 47 °F	3.66	
COP at 5 °F	1.85	









**SPECIFICATIONS** 

LINE SET REQUIREMENTS		
Connection Type	Flare	
Liquid	Ø1/4" (Ø6.35mm)	
Gas	Ø3/8" (Ø9.52mm)	
Pre-Charge Length	25'	
Minimum Length	10'	
Maximum Length	82'	
Maximum Height Differential	33'	
Additional Refrigerant (oz./ft)	0.16	

OUTDOOR UNIT		
Unit Dimensions	Width	30 1/8"
	Depth	11 15/16"
	Height	21 7/8"
	Width	34 15/16"
Carton Dimensions	Depth	13 1/4"
	Height	24"
Net Weight	63.7 lbs.	
Gross Weight	69.0 lbs.	
Cooling Operating Temperature	5 °F – 122 °F	
Heating Operating Temperature	-13 °F - 75 °F	
Voltage/Phase/Frequency	208–230V, 1 Phase, 60 H	
Voltage Range	187-253V	
Recommended Breaker (Amps)	15	
Minimum Circuit Ampacity (Amps)	13	
Communication Wire Size	14*4 AWG Stranded	
Rated Current – Cooling (Amps) <sup>1</sup>	2.66	
Rated Current - Heating (Amps) <sup>2</sup>	3.48	
Sound Pressure (dB(A))	53	

1	Measured	at	95	٥F

<sup>&</sup>lt;sup>2</sup> Measured at 47 °F.

INDOOR UNIT		
Unit Dimensions	Width	31 9/16"
	Depth	7 7/8"
	Height	11 5/8"
	Width	34 7/16"
Carton Dimensions	Depth	11 1/4"
	Height	14 15/16"
Net Weight	19.0 lbs.	
Gross Weight	24.3 lbs.	
Indoor Unit Air Flow (CFM)	Low	153
	Medium	194
	High	291
Moisture Removal (Pints/day)	37.2	
Drain Port O.D.	Ø5/8" (Ø16mm)	
Recommended Breaker (Amps)	15	
Sound Pressure (dB(A))	Low	24
	Medium	34
	High	40

COMPRESSOR		
Туре	DC Rotary Inverter	
Oil Type	Ester Oil VG74	
Oil Charge (oz.)	10.5 (310 ml)	


 $<sup>^3</sup>$  Sensible Capacity: Indoor 80 °F DB, 67 °F WB // Outdoor 5 °F DB, 4 °F WB

 $<sup>^4</sup>$  Maximum Capacity: Indoor 70 °F DB, 67 °F WB // Outdoor 5 °F DB, 4 °F WB




**IDU DIMENSIONS - DRAW09F1B** 


### **Unit Dimensions**



## **Mounting Plate Dimensions**




#### **Clearance Distances**






**ODU DIMENSIONS - DRA1U09S1B** 

#### **Clearances**



#### **Dimensions**





#### NOTE

Illustrations in this document are for explanatory purposes. The actual shape of your mini–split equipment may vary slightly.