

# Lovibond® Water Testing

## Tintometer® Group



### TB350 WL

Laboratory accuracy meets portability



- Reads up to 4000 NTU without the need for dilutions
- Fast Settling Mode increases accuracy of readings with large or heavy particles
- Easily save and recall measurement data sets
- US EPA Approved (alternative to method 180.1)

Part Number: 194310

Ideal for field and environmental testing, the TB350 turbidimeter delivers the most reliable measurements for low range to high range samples without sacrificing accuracy. Featuring the patent-pending Multipath 90° BLAC® sensor technology, the optical system is engineered with dual detectors to deliver a ratio reading which mitigates common measurement stability issues.

The intuitive, touchscreen interface makes it easy to perform procedures and interpret results. With function applications, you can navigate between settings and performing that function efficiently. This user interface eliminates common frustrations and prevents errors. The data logging capabilities allow you to record the testing location, operator's identification, time and date along with the measurement. Stored data can be transferred to a computer via USB.

Supplied ready-to-use with sample cells, silicone oil and calibration standards in carrying case.

At Lovibond®, we look out for the little things that make a big difference. On the surface, turbidity analysis is a simple measurement. However, there are many factors that can affect the accuracy of readings or the dependability of an instrument. We obsess about turbidity measurement so you don't have to. Our team of globally recognized turbidity experts work to anticipate and solve operators' struggles with turbidity measurement.

#### Industry

Municipalities

#### Application

Drinking Water Treatment | Pool Water Control |  
Pool Water Treatment | Waste Water Treatment

#### TB350 WL

The TB350 WL portable turbidimeter is designed for use in the field. Distribution system monitoring, environmental testing or even labs that test a wide range of samples are ideal applications. The instrument includes features and tools to prevent common turbidity measurement mistakes and encourage best practices to ensure the best results.

#### Measuring Range

Test Name	Measuring Range
Turbidity	0.01 - 4000 NTU

Technical Data

Model	Model WM-040-1001 (WL)
Light Source	White LED
Regulatory Compliance	EPA approved (alternative to US EPA 180.1)
Measuring Principle	Nephelometric (Multipath 90° BLAC)
Measuring Range	0.01 - 4000 NTU (FNU)
Accuracy	± 1.8 % of reading + straylight
Stray Light	< 0.014 NTU
Display Units	NTU, FNU, Degrees, mg/L Kaolin, mg/L PSL
Reading Modes	Single, Signal Averaging, Fast-Settling
Calibration Options	Full-range calibration from 0 - 4000 NTU
Detector	Silicon Photodiode
Sample Required	10 mL (0.4 oz)
Display	Full-Colour Touchscreen
Display Size	55 x 95 mm (W x H)
Interfaces	USB-A USB-C
Data Logger	250 measurements, all calibrations, verifications and factory-restore actions
Data Transfer Format	.csv
Power Supply	4 batteries (AA) 3 NiMH-battery pack (AA) Universal (90 - 240 VAC), via external power supply
Compliance	CE CSA FCC A RoHS TÜV UL WEE
Languages User Interface	German, English, French, Spanish, Portuguese, Chinese, Japanese, Dutch, Turkish, Polish
Languages Quick Start Guide	German, English, French, Spanish, Italian, Portuguese, Chinese, Dutch, Turkish, Russian
Languages Full User Manual	German, English, French, Spanish, Italian, Portuguese, Chinese, Dutch, Turkish, Russian
Dimensions	6.1 x 3.27 x 8.86"
Weight with Packaging	(898 g with four AA alkaline batteries)

Accessories

Title	Part Number
Set turbidity standards T-CAL (5, 20, 800, 2000, 4000 NTU)	194152
Silicon oil	194295
Batteries (AA), set of 4	1950025
Cleaning cloth	197635
Sample cuvettes with black lid, Height 55 mm, ø 24 mm, set of 12	197655
USB-C cable 1 m, USB-C to A	19820-081
Power supply TB series	19820-170
Brush, 11 cm length	380230
Cuvette stand for 6 round cuvettes Ø 24 mm	418951
T-CAL®-Standard, 4000 NTU, 125 ml	48012912
T-CAL®-Standard, 4000 NTU, 500 ml	48012950

Delivery Scope

- TB350 WL in case
- [2 cuvettes with lids](#)
- [1 Cleaning cloth for cuvettes](#)
- [1 Cleaning brush](#)
- [Silicon oil, 15 mL](#)
- [4 Batteries \(AA\)](#)
- 1 T-CAL®-Standard, 5 NTU
- 1 T-CAL®-Standard, 20 NTU
- 1 T-CAL®-Standard, 800 NTU
- 1 T-CAL®-Standard, 2000 NTU
- 1 T-CAL®-Standard, 4000 NTU
- 1 Screw driver
- 1 Quick Start Guide
- 1 Test Certificate T-CAL®
- 1 Warranty information

---

**Tintometer GmbH**  
Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

**The Tintometer Limited**  
Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

**Tintometer China**  
Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

**Tintometer South East Asia**  
Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

**Tintometer Brazil**  
Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@tintometer.com.br  
www.lovibond.com.br  
Brazil

**Tintometer Inc.**  
6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.com  
USA

**Tintometer India Pvt. Ltd.**  
Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

**Tintometer Spain**  
Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain