


aquatherm greenpipe® - tee


Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	l	z	D	Weight
	Nom. I.D.	pc	[in]	[in]	[in]	[in]	lb/pc
0113106	3/8"	10	0.63	0.87	0.35	0.96	0.03
0113108	1/2"	10	0.79	1.00	0.43	1.16	0.05
0113110	3/4"	10	0.98	1.22	0.59	1.34	0.07
0113112	1"	5	1.26	1.38	0.67	1.69	0.14
0113114	1.25"	5	1.57	1.59	0.79	2.05	0.20
0113116	1.5"	5	1.97	1.95	1.02	2.68	0.45
0113118	2"	1	2.48	2.36	1.28	3.31	0.81
0113120	2.5"	1	2.95	2.70	1.52	3.94	1.23
0113122	3"	1	3.54	3.11	1.81	4.72	2.13
0113124	3.5"	1	4.33	3.66	2.20	5.79	3.79
0113126	4"	1	4.92	4.59	3.01	6.57	5.89

aquatherm greenpipe® - tee

Material : **fusiolen®** PP-R
 Pipe Series : SDR 6 and up
 In accordance with : NSF-14, NSF-51, NSF-61, CSA-B137.11,
 ICC AC 122, ICC ESR 1613, ASTM F 2389,
 CFIA #A508, ICC PMG-1014, IAPMO
 Color : green



Art.- No.	Dimension	PU	d	z	Weight
	Nom. I.D.		[in]	[in]	lb/pc
0113130	6" -- (SDR 7.4)	1 pc	6.30	5.71	8.05
0113131	6" -- (SDR 11)	1 pc	6.30	5.71	6.11
0113134	8" -- (SDR 7.4)	1 pc	7.87	9.84	8.05
0113135	8" -- (SDR 11)	1 pc	7.87	9.84	15.15
0113138	10" -- (SDR 7.4)	1 pc	7.87	14.76	48.51
0113139	10" -- (SDR 11)	1 pc	7.87	14.76	35.28