


Lighted MEDICINE CABINET




FEATURES/TYPICAL SPECIFICATIONS

- Recess Mount Installation
 - Wall Opening/Rough-in Dimensions: 14" x 19" x 3½"
- One piece drawn steel housing (HY/ST)
 - 24 gauge steel with white, heat cured, acrylic paint finish
- Frame Mirror door
 - Polished stainless steel frame (SS8)
 - 2mm float glass mirror door front
 - 26 gauge steel door back with white, heat cured, acrylic paint finish
- 90° continuous piano hinge (HG01)
 - 16" hinge is welded to the door and mechanically fastened to housing
- Right-hand door swing
- High-impact polystyrene shelves, adjustable (ADJ) (2 typical)
 - Multiple shelf positions via lances punched in the sides of the cabinet housing
- Fluorescent side lights (F15T8CW) included
 - Grounded switch and convenience outlet, UL Listed
Outlet located on right side; bottom of the cabinet
- Mounting hardware included
- Standard Pallet Quantity of 24 units

Finishes:

Housing: PT01—Basic White
 Mirror: Flat mirror
 Frame: SS8—Polished Stainless Steel



DIMENSIONS IN INCHES*

Model #	Description	DIMENSIONS IN INCHES*					
		A	B	C	D	E	F
455FL	Lighted cabinet 1DR 20X22 SS8 2LT	20%	22¼	¾	13½	18½	3½

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by
			Date

* All models and material specifications are subject to change or withdrawal without notice.