

SUBMITTAL COVER SHEET

PROJECT NAME		
SUBMITTED BY	DATE	

Indoor Unit (IDU): DRAL06F1A	Outdoor Unit (ODU): DRA1U09S1B	Wireless Remote Control
	DURASTAR)	

PRODUCT FEATURES

- Low ambient heating down to -13°F
- Low ambient cooling down to 5°F
- Wireless Remote Control with "Follow Me" Technology
- Variable Speed Inverter Compressor
- Auto Restart
- Sleep Mode
- Turbo Mode
- Quiet operation
- 46°F Freeze Protection
- Included base pan heater
- Refrigerant leak detection
- Anti-corrosive fin coating
- · Grille included

CAPACITIES		
Cooling Capacity (BTU/hr)	Rated at 95°F1	6500
	Minimum	3600
	Maximum	11200
Heating Capacity (BTU/hr)	Rated at 47°F²	7100
	Rated at 5°F³	8000
	Minimum	3700
	Maximum	12500

SYSTEM DATA	
Refrigerant Type	R-410A
Refrigerant Charge (oz.)	38.1
Design Pressure (PSIG)	550/340
Indoor/ Oudoor Coil Coating	Golden Fin Coating

EFFICIENCY DATA	
SEER2	22.0
EER2	14.5
HSPF2	10.8
SEER	22.0
EER	14.5
HSPF	10.6
COP at 47°F	3.8
COP at 5°F	2.0









INDOOR UNIT

Unit Dimensions

Carton Dimensions

Net Weight

Gross Weight

Drain Port O.D.

Drain Pump Lift

Indoor Unit Air Flow (CFM)

Recommended Breaker (Amps)

Sound Pressure (dB(A))

SPECIFICATIONS

50-5/16" 13-13/16"

9"

57-5/8

22-1/2"

22-1/2"

235

259

294

32.5

35.5

37.5

58 lbs.

81 lbs.

1"

20.8"

15

Width

Depth

Height Width

Depth

Height

Low

High

Low

High

Medium

Medium

LINE SET REQUIREMENTS		
Connection Type	Flare	
Liquid	Ø1/4" (Ø6.35mm)	
Gas	Ø3/8" (Ø9.52mm)	
Pre-Charge Length	25'	
Minimum Length	10'	
Maximum Length	82'	
Maximum Height Differential	33'	
Additional Refrigerant (oz./ft)	0.16	

OUTDOOR UNIT		
	Width	30-1/8"
Unit Dimensions	Depth	11-15/16"
	Height	21-7/8"
	Width	34-15/16"
Carton Dimensions	Depth	13-1/4"
	Height	24"
Net Weight	63.7	lbs.
Gross Weight	69.0 lbs.	
Cooling Operating Temperature	5°F - 122°F	
Heating Operating Temperature	-13°F	- 75°F
Voltage/Phase/Frequency	208-230V, 1	Phase, 60 Hz
Voltage Range	187-	253V
Recommended Breaker (Amps)	1	5
Minimum Circuit Ampacity (Amps)	1	3
Communication Wire Size	14*4 AWG	Stranded
Rated Current – Cooling (Amps) ¹	3.00	
Rated Current – Heating (Amps) ²	4.	33
Sound Pressure (dB(A))	53	

COMPRESSOR	
Туре	DC Rotary Inverter
Oil Type	Ester Oil VG74
Oil Charge (oz.)	10.5 (310 ml)


¹ AHRI Rated at 95°F (AFull).


² AHRI Rated at 47°F (H1Full).


³AHRI Rated Capacity at 5°F (H42)




IDU DIMENSIONS - DRAL06F1A













ODU DIMENSIONS - DRA1U09S1B

Clearances



Dimensions



NOTE

• Illustrations in this document are for explanatory purposes. The actual shape of your mini–split equipment may vary slightly.