



BADGER BOOTS™

Waterproof, Durable Comfortable Boots For Any



**The Badger works as hard as you to get the job done....
no matter the conditions**

Ultra-comfortable Badger Boots™ are 100% liquidproof and feature breathable Neoprene uppers* with extra width in the calf area for a more relaxed fit. A cushioned footbed helps absorb impact shock and a steel shank provides arch support when ladder climbing or digging with shovels. The high quality outsoles are abrasion resistant for long life and will remain flexible in cold temperatures. A cushioned, removable insole helps wick moisture to keep feet and dry for optimum protection and extraordinary comfort.

- 15" Ht. - Steel Toe.
- Meets ASTM F2413 M/I/C EH** for safety toe caps and Electrical Hazard protection.
- Steel shank for added arch support.
- High quality rubber and 5mm Neoprene with 2mm Airmesh construction are 100% waterproof and durable.
- Ultra comfortable breathable Neoprene upper with extra width in the calf area for a more relaxed fit.
- Reinforced heel cup improves comfort and improves stability to help prevent ankle turns.

Works as hard as you to get the job done



The self-cleaning cleated outsole provides traction on indoor and outdoor surfaces.

Ideal Applications: Food Processing, Transportation, Utilities, Construction, General Industry, Municipalities, and Agriculture.

Chemical Resistance: Acids, alcohols, bases, and diluted water solutions of most chemicals that are water soluble. Not recommended for constant contact with petroleum and oil based products.



- Snugleg last design hugs the foot for all day working comfort.
- Heel kick for easy hands free removal.
- Removable, cushioned insole helps wick moisture to keep feet warm and dry.
- Self-cleaning cleated outsole provides traction on indoor and outdoor surfaces.

BADGER BOOTS™

■ ■	87251	Black Upper – Black Cleated Outsole – Ht. 15" – Steel Toe – Steel Shank	4 - 11
■ ■	80151	Insulated - Black Upper – Black Deep Lug Cleated Outsole – EVA Midsole - Ht. 17" – Plain Toe	4 - 11
■ ■	87121	Black Upper – Black Cleated Outsole – Ht. 12" – Plain Toe – Steel Shank	4 - 11
■ ■	87151	Black Upper – Black Cleated Outsole – Ht. 15" – Plain Toe – Steel Shank	4 - 11

* The insulated style #80151 features a fleece-lined upper and an EVA midsole to insulate your feet from cold and ground. No steel shank in the insulated style.
 ** Boot shall withstand 18,000 volts at 60 HZ for 1.0 second under dry conditions tested as per lab conditions in ASTM F2412. Electrical Hazard features of the soles and heels are intended to protect against electrical hazards due to accidental contact with live electrical energized conductors, parts or apparatus, Electrical Hazard soles and heels are not intended for wear in environments where volatile chemicals or explosive vapors are present, where conductive footwear is required, and where electrical hazard features of the soles and heels will deteriorate in wet environments, and when worn on wet surfaces.

#4067 – 9/19

TINGLEY

est. 1896

ISO 9001 Certified
www.tingleyrubber.com

1•888•593•7091

