



SubSurface Leak
Detection, Inc.®

MODEL LD-15 PROFESSIONAL'S LEAK SURVEY INSTRUMENT



Displaying leak loudness at a water meter



Pinpointing a water leak directly over the pipe



Surveying for water leak sounds at a meter



Surveying for water leak sounds at a hydrant

LD-15 PROFESSIONAL'S LEAK SURVEY INSTRUMENT




Standard Items

- ① Amplifier with Meter Display and Filter Controls
- ② Padded Case and Standard Belt (40 inches)
- ③ High Sensitivity Sensor and Cable
- ④ Base Plate for Listening on Street Surfaces
- ⑤ Aviation-Grade Stereo Headphones
- ⑥ Heavy-Duty ABS Plastic Carrying Case

Features

- High sensitivity sensor with Neodymium magnet (extra strong). Sensor and cable connection completely sealed and water-proof (submersible).
- Amplifier with superior audio quality (very low distortion and superior signal-to-noise ratio) and large meter display. Press the Mute Switch to hear sounds when you are ready.
- "Survey" for water leaks by listening at hydrants and valves with the sensor and magnet. Survey at water meters with a Long Contact Rod (optional).
- "Pinpoint" water leaks in pipes under asphalt or concrete with the base plate attached to the sensor and magnet.
- Use the High filter range for water leak surveying. Use the Low filter range for water leak pinpointing. High frequency leak sounds travel on the pipes, but only low frequencies pass through the soil.



LD-15
sensor
with base
plate

Optional Accessories

- ⑦ 40 inches Long Contact Rod (not shown)
- ⑧ 60 inches Long Contact Rod (not shown)
- ⑨ Large Size Belt (50 inches)
- ⑩ Extra Large Size Belt (60 inches)

Specifications

Amplifier

- Amplification : 56 dB
- Filter Ranges : 1) High Range
30 Hz to 5000 Hz
2) Low Range
30 Hz to 800 Hz
3) Notch Filter
150 Hz, 180 Hz
- Power : 4 C dry cell batteries
- Battery Life : 80 hours with alkaline batteries
at 68 degrees F
- Weight : 31 ounces (including 4 C batteries)
- Size : 6.4" x 3.0" x 5.7"
(163mm x 76mm x 144mm)

Sensor

- Sensitivity : 10 V/g
- Resonance Frequency : 950 Hz (± 150 Hz)
- Weather Protection : IP68 or equivalent
(3 ft under water for 3 hours)
- Cable Length : 9.75 ft

Distributed by:

Pollardwater™