

Features

- Metal construction
- For 4" (10.2 cm) centers
- 4-1/4" (10.8 cm) spout reach
- Grid drain with tailpiece
- Stationary spout
- Available with sculpted acrylic handles [-7] or lever handles [-4]
- Complements the Coralais Suite
- 1.5 gallons (5.7 liters) per minute maximum flow rate

CENTERSET LAVATORY FAUCET K-15243

ADA

CSA B651



OBC



Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:



- ADA
- ICC/ANSI A117.1
- CSA B651
- OBC
- ASME A112.18.1/CSA B125.1
- NSF 61
- EPA WaterSense®
- All applicable US Federal and State material regulations



Colors/Finishes

- CP: Polished Chrome

Specified Model

Model	Description	Lever Handles 	Sculptured Acrylic Handles 
K-15243-4	Centerset lavatory faucet - Accessibility compliant lever handles	<input type="checkbox"/> CP	
K-15243-7	Centerset lavatory faucet - with sculptured acrylic handles (shown)		<input type="checkbox"/> CP

Optional Accessories

1160594	Large Spray 0.35 gpm (1.32 lpm) – Insert only	<input type="checkbox"/> NA
_____	Additional flow options are available (refer to the Price Book)	<input type="checkbox"/> NA

PRODUCT SPECIFICATION


The two-handle centerset lavatory faucet shall be made of metal construction. Product shall feature a maximum flow rate of 1.5 gallons (5.7 liters) per minute. Product shall be for 4" (10.2 cm) centers. Product shall feature a 4-1/4" (10.8 cm) spout reach and a grid drain with tailpiece. Product shall be available with sculpted acrylic handles [-7] or lever handles [-4]. Product shall complement the Coralais Suite. Faucet shall be Kohler Model K-15243-____-____.

CORALAIS®

Installation Notes

Install this product according to the installation guide.

ADA, CSA B651, OBC compliant when installed to the specific requirements of these regulations.



Product Diagram