

EBARA

Model EPD / OPTIMA Pro Drainer™ sump, drainage



EBARA

EBARA Pumps Americas Corporation

Model EPD/OPTIMA

Features

- High quality stainless steel (*Note:* Optima has Noryl impeller)
- Available in 1/3, 1/2, 3/4, 1, 1 1/2 HP models • **Single and three phase models available**
- Air filled, continuous duty rated, permanent split capacitor motors •

Built-in thermal protection with automatic reset (Single Phase Only)

- Built to **operate whether fully or partially submerged**
- Oil lubricated double mechanical shaft seal (1/2 - 1 1/2 HP models)
- Temperature rating to 122°F/50°C; 140°F/60°C intermittent duty
- 20' UL/CSA approved, water resistant #16 AWG cord
- Capacities to 88 GPM, heads to 62 feet
- Optima slimline automatic models **can operate in a 12" diameter or 8" x 8" square basin**


Applications

- Residential
- Commercial
- Industrial
- Drainage
- Seepage
- Effluent/containment transfer
- Waste water (from trays, wet bars, washing machines)
- Empty water storage structures
- Decorative fountains
- Irrigation
- Mound systems, leach fields
- Move water/effluent to sewage systems



**Note: UL and CSA listed; Model Optima UL certified only.*

EPD, Optima selection chart



EBARA Pumps Americas Corporation

1651 Cedar Line Drive • Rock Hill, SC 29730 • telephone: (803) 327-5005 • fax: (803) 327-5097

www.pumpsebara.com

© 2018 EBARA Pumps Americas Corporation, All rights reserved.