

Engineered Plastic (EP) Flow-through Vertical Multi-port Tee

Submittal Information

Revision B: June 7, 2010

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:


Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	UDELE [®] Polysulfone GF120
Maximum Temperature (no pressure):	320°F (160°C)
Maximum Working Temperature/Pressure:	210°F at 150 psi (99°C at 10.3 bar)



Product Information and Application Use

The Uponor Engineered Plastic (EP) Flow-through Vertical Multi-port Tee is designed for use in hot and cold domestic potable water distribution systems. The EP Flow-through Vertical Multi-port Tee is available with 3/4" ProPEX[®] inlets.¹ All outlets feature 1/2" ProPEX connections.

✓ Description	Part Number	A	B	C	D	E	Weight
EP Flow-through Multi-port Vertical Tee, 3 outlets, 3/4" x 3/4" x 3/4" ProPEX	Q2237757	6.03"	2.85"	1.25"	0.75" ProPEX	0.75" ProPEX	0.12 lbs.
EP Flow-through Multi-port Vertical Tee, 4 outlets, 3/4" x 3/4" x 3/4" ProPEX	Q2247757	7.28"	2.85"	1.25"	0.75" ProPEX	0.75" ProPEX	0.16 lbs.

Installation

The installer can use any product designed to mount 1" copper pipe (for the 3/4" EP Flow-through Vertical Multi-port Tee) as a mounting bracket. For more information, refer to the Uponor Professional Plumbing Installation Guide or Uponor Radiant Floor Heating Installation Handbook.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14 and 61 certified; ICC ESR 1099; IAPMO 3946

Related Applications

PEX-a Plumbing Systems
Radiant Heating and Cooling Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-1409
www.uponor-usa.com

Uponor Ltd.
2000 Argenta Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX[®] is a registered trademark of Uponor, Inc. ProPEX[™] is a trademark of Uponor Ltd.