

5 Gallon Steel Safety Can for Flammables, Type I, Flame Arrester, Red - 7150100

Product Images





Short Description

- Color coding avoids accidents
- Self-closing lid controls spills
- Leakproof, auto-venting lid prevents explosion
- Approved by FM, UL/ULC, and TUV; also meets OSHA and NFPA requirements

Description

Designed with a single spout for filling and pouring, the sealed lid features automatic positive-pressure relief that vents between 3 and 5 psig (0.2 and 0.35 bar) to guard against rupture or explosion.

Made from high-grade coated steel, each can is tested to guarantee 100% leakproof construction. The tough powder-coat finish resists chemicals and stands up to demands of rigorous use. Each Justrite safety can is equipped with a stainless steel flame arrester which dissipates heat to stop flashback ignition. Cans up to 1 quart (1L) feature a trigger-release handle, while larger capacities have a swinging handle to greatly ease carrying of heavier loads.

Use a Type I safety can funnel to pour into smaller openings. This polypropylene funnel attaches to the spout neck of Type I Safety cans that are sized 1-gallon (4L) and larger. The two-position funnel folds down for when you fill or store the can, and stays up for when you pour. Large rounded bowl provides protection from splashing and spillage. Durable construction holds up to heavy use.

Specifications

| | |
|----------------------------|-------------------------------|
| Model No | 7150100 |
| UPC | 697841140189 |
| Badge | Best Seller |
| International Model No. | 7150100Z |
| Pallet Quantity | 48 |
| FM Approval | Yes |
| UL Approval | Yes |
| ULC Approval | Yes |
| TUV Approval | Yes |
| OSHA Compliance | Yes |
| Complies with NFPA Code 30 | Yes |
| CARB Compliance | Yes |
| Color | Red |
| Material Specifications | Steel |
| Dimensions, Exterior | 16.875" H x 11.75" Outer Dia. |
| | 429mm H x 298mm Outer Dia. |
| Capacity | 5 gallon |
| Liter Capacity | 19 |
| Fill/Pour Hole inch | 1.58 |
| Fill/Pour Hole mm | 40 |
| Net Weight, lbs | 6.2 |
| Net Weight, kg | 2.8 |