

Optima® SMEDTH® 111-1.28

Description

Exposed, Battery Powered, Sensor Activated, Sloan® Optima® SMOOTH® Water Closet Flushometer for floor mounted or wall hung top spud bowls.

Flush Cycle

☐ Model 111-1.28 High Efficiency (1.28 gpf/4.8 Lpf)

Specifications

Quiet, Exposed, Diaphragm Type, Chrome Plated Closet Flushometer with the following

Flushometer

- High Chloramine Resistant PERMEX® Synthetic Rubber Diaphragm with Dual Filtered Bypass
- ADA Compliant Metal Oscillating Non-Hold-Open Handle with Triple Seal Handle Packing
- 1" I.P.S. Screwdriver Bak-Chek® Angle Stop
- Vandal Resistant Stop Cap
- Adjustable Tailpiece
- · Vacuum Breaker with Flush Connection
- Spud Coupling and Spud Flange for 11/2" Top Spud
- Sweat Solder Adapter with Cover Tube and Cast Wall Flange
- High Copper, Low Zinc Brass Castings for Dezincification Resistance
- Non-Hold-Open Handle and No External Volume Adjustment to Ensure Water Conservation
- · Low Consumption flush accuracy
- Handle Packing, Stop Seat and Vacuum Breaker Molded from PERMEX® Rubber Compound for Chloramine Resistance

Optima SMOOTH Unit

- ADA Compliant OPTIMA® SMOOTH® Battery Powered Infrared Sensor for automatic "Hands-free" operation
- · Sensor with Automatic Range Adjustment
- Chrome Plated Metal Sensor Housing
- Mechanical Manual Override Flush Handle
- Four (4) Size C Batteries included
- "Low Battery" Flashing LED
- "User in View" Flashing LED
- 25 to 80 psi Operating Range

Valve Body, Cover, Tailpiece and Control Stop shall be in conformance with ASTM Alloy Classification for Semi-Red Brass. Valve shall be in compliance to the applicable sections of ASSE 1037, ANSI/ASME A 12.19.2.

Variations

 \Box TP

 $\overline{\ } \ \underline{\ } \ \underline{\$ Extended Bumper on Angle Stop (for seat with cover)







Sloan Valve Company is buying renewable energy certificates to meet 100% of the company's purchased electricity use at its Franklin Park, Illinois facility.

This space for Architect/Engineer approval	
Job Name	Date
Model Specified ————	Quantity
Variations Specified	
Customer/Wholesaler —	
Contractor	
Architect	



ADA Compliant

Automatic

Sloan SMOOTH® equipped Flushometers provide the ultimate in sanitary protection and automatic operation. There is no need for AC hookups or wall alterations. The Flushometer operates by means of a battery powered infrared sensor. Once the user enters the sensor's effective range and then steps away, the SMOOTH® Unit initiates the flushing cycle to flush the fixture. State-of-the-art Technology enables activation of a manual override without "double flushing" occurring as the user departs (locks out sensor for approximately 10 seconds).

Hygienic

The Sloan® Optima® SMOOTH® Flushometer is the next advancement in hygiene. It uses sensor technology to transform manual installations into electronic, hands-free operation. User makes no physical contact with the Flushometer surface except to initiate the Override Handle when required. Helps control the spread of infectious diseases.

Economical

Automatic operation provides water usage savings over other flushing devices. Reduces maintenance and operation costs. Installation and battery replacement does not require turning off water to the valve.

Warranty

3 year (limited)

111-1.28

Description

Exposed, Battery Powered, Sensor Activated, Sloan® Optima® SMOOTH® Water Closet Flushometer for floor mounted or wall hung top spud bowls.

► Flush Cycle

☐ Model 111-1.28 High Efficiency (1.28 gpf/4.8 Lpf)

OPERATION


 A continuous, invisible light beam is emitted from the SMOOTH unit's Infrared Sensor.



2. When the user enters the sensor's effective range, the Red LED light in the sensor window flashes for eight seconds. After eight seconds of sensing the user, the light will stop flashing and the unit waits for the user to step away before initiating a flush cycle.



3. When the user steps away, the unit initiates a flush cycle. The unit then automatically resets and is ready for the next user.



ELECTRICAL SPECIFICATIONS

- Control Circuit
 6 VDC Input
- OPTIMA Sensor Type
 Active Infrared with Automatic
 Adjustment
- OPTIMA Sensor Range
 Normal Range:
 26" 32" (660 mm-813 mm)
 Reduced Range:
 20" 26" (508 mm-660 mm)
- Battery Type
 (4) Size C Alks

(4) Size C Alkaline

Battery Life


2 Years @ 4,000 Flushes/Month

Indicator Lights
User in View/Low Battery


Operating Pressure

25-80 psi (172-552 kPa)

DIMENSIONS



Side View



Top View