Liberty Pumps[®]

NEW!

Alarms for Sump, Sewage and Effluent



ALM-2 (20' float cord) ALM-2-1 (10' float cord)

- Nema 1 Indoor rated
- 115V operation with 9 volt battery back-up
- 86 decible horn
- Red alarm light
- Green "power-on" light
- Low battery chirp
- Automatic reset
- Test / Silence feature



ALM-P1 Alarm with Probe Sensor

- Indoor alarm
- 115 Volt
- 9V battery back-up
- Compact probe mounted sensor (snaps on 1-1/4" or 1-1/2" discharge pipe)

Auto Dialer

- Auxiliary contacts
- Visual and audio alarm



ALM-2W Outdoor

- Meets Type 3R water-tight standards
- 115V operation
- Thermoplastic enclosure
- Red alarm beacon, 360° visible
- 85 decible horn
- Test / Silence switch
- 20' Float cord



Call your cell phone

Call your plumbing contractor

Call your family

Call your neighbor

On vacation or away from home?

Get notification of an alarm condition dialed directly to

- Can sequentially dial up to 4 telephone numbers
- Delivers up to a 16 second message you can record
- 120 VAC

your phone!

- 9 V. Battery Back-up
- Mounts flat on wall
- Ability to program a pause and pound (#) tone into dialing sequence
- For indoor mounting only
- LED display

NOTE: this unit requires auxiliary contacts on the source alarm or control panel



ALM-3W Commercial Outdoor

- Nema 4X rated
- Commercial-duty enclosure
- 115V operation. Direct wire.
- Red alarm beacon, 360° visible
- 88 decible horn
- Alarm "Test / On / Silence" switch
- 20' float cord
- Includes auxiliary contacts

Liberty Pumps 7000 Apple Tree Avenue • Bergen, NY 14416 Phone 800-543-2550 Fax (585) 494-1839 www.libertypumps.com