
P50/P100 SERIES

I/2 and I HP Effluent ST.E.P. Pumps

Specifications		
Applications	Effluent Removal, Sump Drainage, Water Transfer, Flood Control	
Capacities	60 GPM	227 LPM
Shut-off Head	124'	37.8 m
Max. Spherical Solids	3/4"	I9 mm
Liquids Handling	domestic, effluent and drain water	
Intermittent Liquid Temperature	up to I40°F	up to 60°C
Motor Electrical Data	I/2 HP, II5V or 230V, IØ; I HP, 230V, IØ, oil-filled, permanent split capacitor type, 3450 RPM, 60Hz	
Acceptable pH Range	6-9	
Specific Gravity	.9-1.1	
Viscosity	28 – 35 SSU	
Discharge, NPT	I-I/2"	38.1 mm
Housing	cast iron	
Minimum Sump Diameter Simplex: Duplex:	24" 36"	61 cm 91.4 cm
Power Cord	20', 14/3 SJOW, SJOW-A	





FEATURES

- P Series effluent pumps are designed for years of maintenance-free operation
- Single-vane, enclosed impeller provides steep, nonoverloading performance curve for pressure collection and ST.E.P. systems; outperforms most pumps in its class
- Enclosed impeller eliminates the possibility of jamming or corrosion between impeller and volute
- Passes 3/4" spherical solids
- Durable motor will deliver many years of reliable service
- Oil-filled motor for maximum heat dissipation and continuous bearing lubrication
- High-torque, permanent split capacitor (PSC), single-phase motors; no starting switches or relays to wear out
- Double tandem seal configuration for extra motor protection, tough effluent pumping applications
- Optional seal leak probes warn of seal leak condition; helps prevent costly motor damage
- On-winding current and temperature-sensitive overload to protect against costly burnout
- Volute seal ring is replaceable; restores pump to original performance if wear should occur
- Motor is held in place by 4 screws; easily removed if service is ever needed
- CSA Listed

