PATRIOT

LIGHT-DUTY COMMERCIAL ELECTRIC WATER HEATERS



Designed for use as recovery heaters for light-duty hot water supply service. Patriot™ PCE water heaters are available with tank capacities from 6 through 119 gallons. They can be installed for non-simultaneous and single element operation (maximum input up to 6 KW), or for simultaneous dual-element operation (maximum input up to 12 KW).

Zinc-Plated Copper Sheath Heating Elements Standard

- Medium watt density design disperses element temperature over larger surface contact area to minimize scale buildup, maximize efficiency and prolong element life
- Element options from 1.5 KW to 6 KW (non-simultaneous or simultaneous operation), recoveries from 6 gph to 49 gph at 100°F rise

Standard Voltages for Easy Installation

- 120V, 277V single-phase, and 208V, 240V and 480V unbalanced 3-phase delta
- Easily converted to single-phase at terminal block (except for 208V with 6000 watt elements
- Single-element heater, single-phase only (see chart for dual-element options)

Factory-Installed Terminal Block

Provides electrical service to heater and connects to block

Factory-Wired Controls

 Temperature control (adjustable from 110°F to 170°F on single-element; 120°F to 180°F on dual-element models)

- Manual reset high temperature cutoff per element (dual-element models)
- Factory wired for non-simultaneous operation; easily converted to simultaneous operation

Glass-Lined Tank with Anode Rod

Provides long-lasting protection against corrosion

Maximum Hydrostatic Working Pressure: 150 psi

Meets ASHRAE 90.1b

Other Patriot™ PCE Series Features

- Simplified, color-coded circuitry for ease of service
- Bonderized undercoat on cabinet with baked enamel finish
- Top inlet and outlet openings
- Foam insulation
- Drain valve
- UL-approved field conversion program

Three-Year Limited Tank Warranty

• Consult written warranty shipped with water heater, or contact State for complete information

Page 1 of 4



WATTAGE, RECOVERY AND ELECTRICAL CHARACTERISTICS

UPPER AND LOWER	RECOVERY – GALLONS PER HOUR AT °F RISE			FULL LOAD CURRENT IN AMPERES			
ELEMENT WATTAGE	40°F	100°F	140°F	208V	240V	480V	
NON-SIMU	JLTANEOU	JS AND SIN	GLE-ELEM	ENT OPERATION	-SINGLE-PHASE	POWER	
1500	15	6	4	7.2	6.3	3.1	
2000	20	8	5	9.6	8.3	4.2	
2500	25	10	7	12.0	10.4	5.2	
3000/3000	30	12	8	14.4	12.5	6.3	
4000/4000	41	16	11	19.2	16.7	8.3	
4500/4500	46	18	13	21.6	18.8	9.4	
5000/5000	51	20	14	24.0	20.8	10.4	
6000/6000	61	24	17	28.8	25.0	12.5	
SIMULTANEOU (Both element				-THREE-PHASE 	POWER		
3000/3000	61	24	17	25.0/14.4*	21.7/12.5*	10.8/6.3*	
4000/4000	81	32	23	33.3/19.2*	28.9/16.7*	14.4/8.3*	
4500/4500	91	36	26	37.5/21.6*	32.5/18.8*	16.2/9.4*	
5000/5000	101	41	29	41.6/24.0*	36.1/20.8*	18.0/10.4	
6000/6000	122	49	35	N/A	43.3/25.0*	21.7/12.5	

^{*}Terminal L2 Amperage/Terminals L1 and L3 Amperage

TANK CAPACITY, DIMENSIONS AND WEIGHTS

MODEL	GALLON CAPACITY	NUMBER OF ELEMENTS	DIMENSIONS IN INCHES				APPROX SHIPPING
NUMBER			A	В	С	D	WEIGHT (LBS.)
PCE 6 10MSA	6	1	15-1/2	14-1/4	11	N/A	35
PCE 10 10MSA	10	1	18-1/4	18	12-1/2	N/A	54
PCE 17 10MSA	15	1	26	18	20-1/2	N/A	58
PCE 20 10MSA	20	1	22-1/4	21-3/4	15-3/8	N/A	73
PCE 30 20LSA	30	2	30-7/8	21-3/4	24-1/8	8	100
PCE 40 20LSA	40	2	32-1/4	24	25-9/16	8	125
PCE 50 20LSA	50	2	32-1/4	26-1/2	25-1/8	8	166
PCE 30 20RTA	30	2	34-1/2	20-1/2	N/A	8	98
PCE 40 20RTA	40	2	45-1/8	20-1/2	N/A	8	113
PCE 52 20RTA	50	2	54-7/8	20-1/2	N/A	8	131
PCE 66 20RTA	66	2	60-3/4	21-3/4	N/A	8	176
PCE 82 20RTA	80	2	59-3/8	24	N/A	8	211
PCE 120 20RTA	119	2	62-7/16	29-3/8	N/A	8	326

HEATING ELEMENT AVAILABILITY


INPUT WATTS	120V	208V	240V	277V	480V
1500	YES	YES	YES	YES	NO
2000	YES	YES	YES	YES	YES
2500	YES	YES	YES	YES	YES
3000	YES	YES	YES	YES	YES
3500	NO	NO	YES	NO	NO
4000	NO	YES	YES	YES	YES
4500	NO	YES	YES	YES	YES
5000	NO	YES*	YES*	YES*	YES*
5500	NO	NO	YES	NO	NO
6000	NO	YES**	YES	YES	YES

^{*}Not available in PCE 10 10MSA, PCE 17 10MSA and PCE 30 20RTA.


**A6 non-simultaneous circuit only.

PCE 6 10MSA not available above 2500 W.

PCE 6 10MSA not available in 480V.





TOP VIEWPCE 6 10MSA, PCE 10 10MSA
PCE 17 10MSA, PCE 20 10MSA




FRONT VIEW

PCE 6 10MSA, PCE 10 10MSA PCE 17 10MSA, PCE 20 10MSA







SRGSS01406 September 2007R Page 3 of 4 ©2007 State Water Heaters Company

SUGGESTED SPECIFICATION

The water heater(s) shall be State Patriot TM Model(s), rated at KW, volts,phase, 60
cycle AC. Water heater(s) shall be listed by Underwriters Laboratories and meet ASHRAE 90.1b. Tank(s) shall be
gallon capacity with a recovery capacity of GPH at a temperature rise of°F with/
upper/lower element wattage. Heater(s) shall have 150 psi working pressure and be equipped with extruded high-density
anode rod. All internal surfaces of the heater(s) exposed to water shall be glass-lined with an alkaline borosilicate composition
that has been fused to steel by firing at a temperature of 1600°F. Electric heating elements shall be medium watt density with
zinc-plated copper sheath or Incoloy sheath
Each element shall be controlled by an individually mounted thermostat and high-temperature cutoff switch. The outer jacke
shall be a baked enamel finish and provided with a full-size control compartment for performance of service and maintenance
through a hinged front panel and shall enclose the tank with foam insulation.

Electrical junction box with heavy-duty terminal block shall be provided (except on 120V and 277V [no junction box on PCE 6 10MSA thru PCE 20 10 MSA]). The drain valve shall be located in the front for ease of servicing. Heater tank shall have a 3-year limited warranty as outlined in the written warranty. Fully illustrated instruction manual will be included.

For more information on State® contact: State Water Heaters 500 Tennessee Waltz Parkway, Ashland City, TN 37015 800-365-0024 Toll-free USA www.statewaterheaters.com

SOLID. STATE

