

### Power-Vee Units

### Complete and Ready to Operate

### **Basic Unit Includes:**

- Power Cable Feed
- Variable Speed Motor with Reverse Switch
- Quick-Change Cable Cartridge

PV-A-WC with case, 25 ft. x 1/4" (25HE1-DH), 25 ft. x 3/8" (25HE2) cables, HECS cutter set and one additional cartridge. Boxed Weight 33 lbs.

**PV-B-WC** with case, 25 ft. x 1/4" (25HE1-DH), 35 ft. x 3/8" (35HE2) cables, HECS cutter set and one additional cartridge. Boxed Weight 36 lbs.

**PV-C-WC** with case, 50 ft. x 1/4" (50HE1-DH), 35 ft. x 3/8" (35HE2) cables, HECS cutter set and one additional cartridge. Boxed Weight 39 lbs.

**PV-D-WC** with case, 25 ft. x 5/16" (25HE1-A-DH) cable. Boxed Weight 27 lbs.

**PV-F-WC** with case, 25 ft. x 1/4" (25HE1-DH) cable. Boxed Weight 26 lbs.

To order without case, delete suffix "WC", as PV-A. 220/230

220/230 & 240 Volt/50 Hz and Cordless units are available.



All ball-bearing, double-insulated, reversible motor with variable speed control; 0 - 500 rpm.

Heavy gauge stamped aluminum with inner drum to prevent cable tangling

#### Capacity:

50 ft. of 1/4" or 5/16" cable; 35 ft. of 3/8" cable. All cables are left hand wound and reinforced with a wire rope center.

#### **Cutter Set:**

See below.

#### Cable Cartridges:

Light weight, impact resistant plastic.

#### Power Feed:

Feeds 3/8" cable at 16 feet per minute.

(UL) LISTED and CSA APPROVED

### 5-Piece Cutter Set For Use Only With Cables Having Connectors



Arrow Head Starting Drill



**Boring Gimlet** 







**FAH** Flexible Spring Arrow Head Cutter

# **Options**



Can be used with all standard HECS cutters.

**Closet Auger Attachment** Guides 1/4" or 5/16" cable into bowl





MCC Carrying Case

## The toughest tools down the line.™

