


# CIRCULATOR VALVES & ELBOWS 8201-15 -8211-15 - 300 - 302




**8201-15**  
CIRCULATOR  
SLOTTED STEM  
(threaded ends)

DIMENSIONS (INCHES)			Approx. Weight
SIZE	A-1	B	
1/2	2-27/32	15/16	.30
3/4	2-5/32	1-1/16	.50
1	2-5/8	1-13/32	.80




**8211-15**  
CIRCULATOR -  
SLOTTED STEM  
(solder ends)

DIMENSIONS (INCHES)			Approx. Weight
SIZE	A	B	
1/2	2-3/32	15/16	.20
3/4	2-25/32	1-1/16	.40
1	2-5/8	1-13/32	.70



**300**  
UNION ELBOW  
(threaded end)

DIMENSIONS (INCHES)			Approx. Weight
SIZE	A	B	
1/2	2-3/8	1-1/16	.45
3/4	2-11/16	1-3/16	.64
1	3-1/16	1-7/16	1.00
1-1/4	3-7/16	1-3/4	1.54



**302**  
UNION ELBOW  
(solder end)

DIMENSIONS (INCHES)			Approx. Weight
SIZE	A	B	
1/2	3/4	1-1/4	.39
3/4	3/4	1-1/2	.56

**RATING**

- 150 PSI SATURATED STEAM (8201-15 & 8211-15)
- 400 PSI NON-SHOCK COLD WATER, OIL OR GAS (8201-15 & 8211-15)

**FEATURES**

- BRASS BODY (ASTM - B16)
- BRASS UNION END & TAILPIECE (ASTM-B16) (300 & 302)
- STANDARD PORT OPENING (8201-15 & 8211-15)
- CHROME PLATED BALL (8201-15 & 8211-15)
- ADJUSTBLE PACKING NUT (8201-15 & 8211-15)
- TFE SEATS & SEALS
- 100% FACTORY TESTED

The information presented on this sheet is correct at the time of publication. Hammond Valve reserves the right to change design, and/or material specifications without notice. For the most current information access [www.hammondvalve.com](http://www.hammondvalve.com)