




ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	1	58450		.19 SEAL WELD	(RMPWPS365)
2	2	58408		1 SW PROTECTOR	POLYETHYLENE
3	1	21066	51098	BODY	A105 (HFS)
4	1	30311	50980	BONNET	A105
5	1	32536	59462	CAST DISC NUT	CAST STELLITE
6	1	50011	60679	CS LOCK NUT	A105
7	1	32460	59463	DISC	CAST STELLITE
8	4	50233	60684	FINISHED HEX NUT	F594 304SS
9	1	58326		GREASE FITTING	MFG. STD.
10	2	58323	48092	GROOVE PIN	A479 TYPE 410
11	1	35042	43460	HANDWHEEL	CAST IRON
12	1	40713	38234	NAME PLATE	ALUMINUM
13	1	55178		PACKING CARTRIDGE	FLEXIBLE GRAPHITE
14	1	34052	28223	PACKING GLAND	A105
15	1	32997	59461	STEM	A479 TYPE 410
16	2	50159	21912	STUD BOLT	F593 304SS
17	1	58452		TACK WELD	(RMPWPS555)
18	1	58450		TACK-WELD	(RMP61347)
19	1	34002	28882	YOKE	A105
20	1	58104	21990	YOKE NUT	A582 TYPE 416

NOTE:
PHOSPHATE PER RMP61012.
VALVE TO BE TESTED PER MSS-SP-61 PER RMPVFLT005

X.XX Inches
[XX,X] MM

WEIGHT	21.3 LBS	9.66 Kg
Cv FACTOR	5.8	

CNS	57761	DWN BY	R.Jackson
REV	09	CHK BY	S.B.R.
BY	R.Jackson	RVD BY	
DATE	9-16-2004	DATE	10-25-78

SERIES No:	SW66723-06
ITEM No:	202690
RATING: 6700 PSI • 100F	SPECS: ASME B16.34 LTD
BODY A105 SEAT INT HF DISC CC STEM 13CR	

FLOWERVE Vogt Valves SULPHUR SPRINGS, TEXAS, USA 1 GLOBE VALVE - FORGED STEEL OS&Y - MALE THREAD SEAL WELD BONNET - INTEGRAL SEAT-BODY GUIDED DISC - SOCKET WELD ENDS - CLASS 2680	
51106-2	