
# NEXT GENERATION HIGH LOW SYSTEM

# ECO-MIX TM





 $A=12" +/- \frac{1}{2}" B=34 \frac{1}{4}" C=2 \frac{3}{4}"$ 

## TM-2020B-LF-DT

- Large Type TM Thermostatic water mixing valve, adjustable high temperature limit stop\*, inlet checkstops, wall support, outlet ball valve
- Small Type TM Thermostatic water mixing valve, adjustable high temperature limit stop\*, integral checkstops, outlet ball valve
- 2" inlets, 2" outlet (51mm X 51mm)
- 1 GPM (3.7 l/min) minimum flow capacity
- Color-coded dial thermometer (0 to 140°F, -10 to 60°C)
- Inlet manifold piping
- Locking temperature regulator
- · Factory assembled and tested

This product is certified to meet Low Lead requirements of wetted surface area containing less than 0.25% lead by weight

#### **OPTIONS:**

- \_\_\_\_SUFFIX CP Chrome plated (Material finish may vary)
- \_\_\_\_SUFFIX IT Inlet Thermometers (shipped loose)
- \_\_\_\_SUFFIX TC Test connection (shipped loose)

Valve assembly is ASSE 1017 Certified



Valve assembly is CSA Certified



MIN	MINIMUM FLOW (GPM)	PRESSURE DROP											
		5	10	15)	20	25	30	35	40	45	50	PSI	
(1/	/min)	.3	.7	.97	1.4	1.7	2.1	2.4	2.8	3.1	3.4	BAR	
	1.0	78	113	129	145	163	172	188	197	214	226	GPM	
(;	3.7)	295	428	488	549	617	651	712	746	810	856	l/min	

NOTE: Flow rates will vary depending on existing field conditions. Leonard Valve Company always recommends using CASPAK® sizing software for proper valve sizing and model number applications.

Note: Leonard Valve Company reserves the right of product, or design modifications without notice or obligation.

**CAUTION!** All thermostatic water mixing valves have limitations. They will NOT provide the desired accuracy outside of their flow capacity range. Consult the Flow Capacity Chart and DO NOT OVERSIZE. Minimum flow must be no less than as indicated.

\*NOTE: A limit stop, set for 120°F (49°C), is simply a mechanical setting to prevent excessive handle rotation. If incoming water is hotter than 150°F (65.5°C), the temperature of the factory test, the valve when turned to full HOT may deliver water in excess of 120°F and the limit stop MUST BE RESET BY THE INSTALLER

Engineer's Approval	Job #				
	Arch/Eng.				
	Contractor				

Note: The models shown represent Leonard Products which are believed to be equivalent in type and function to items specified. Leonard Valve Company is not responsible for errors or omissions due to differences in interpretations of information provided.




1360 Elmwood Avenue, Cranston, RI 02910 USA Phone: 401.461.1200 Fax: 401.941.5310

Email: info@leonardvalve.com

Web Site: http://www.leonardvalve.com


### PIPING METHOD

### Method #5 **Shown**



NOTE:
FOR MULTIPLE TEMPERED
LOOPS A BALANCING VALVE AND
CHECK VALVE MUST BE
INSTALLED ON EACH LOOP
AFTER TEMPERED FIXTURES

## (OPTIONAL) TEST CONNECTION





1360 Elmwood Avenue, Cranston, RI 02910 USA Phone: 401.461.1200 Fax: 401.941.5310

Email: <a href="mailto:info@leonardvalve.com">info@leonardvalve.com</a>
Web Site: <a href="mailto:http://www.leonardvalve.com">http://www.leonardvalve.com</a>