
57488-2



ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	1	58450		.25 SEAL WELD	(RMP61701)
2	2	58412		1 1/2 SW PROTECTOR	POLYETHYLENE
3	1	50348		5/8-11 SET SCREW	ASTM F912
4	2	50176	21912	5/8-11 STUD BOLT	F593 304SS
5	1	21135	52070	BODY	A105 (HFS)
6	1	30437	57490	BONNET	A105
7	1	32534	57478	CAST DISC NUT	CAST STELLITE
8	1	32459	57476	DISC	CAST STELLITE
9	4	50236	60684E	FINISHED HEX NUT	F594 304SS
10	1	58326		GREASE FITTING	MFG. STD.
11	2	58322	48092	GROOVE PIN	TYPE 316
12	1	35067	26065	HAND WHEEL	MALLEABLE IRON
13	1	35065	26066	LEVER	MALLEABLE IRON
14	1	41283	38233	NAME PLATE(GREEN)	ALUMINUM
15	4	55143	60636	PACKING	FLEXIBLE GRAPHITE
16	2	55192	60636	PACKING	BRAIDED GRAPHITE
17	1	34078	57493	PACKING GLAND	A105
18	1	58087	57492	PACKING RING	A479 TYPE 410
19	1	58156	26067	RETAINING NUT	A105
20	1	32987	57491	STEM	A479 TYPE 410
21	1	58452		TACK WELD	(RMPWPS555)
22	1	58450		TACK-WELD	(RMP61347)
23	1	34003	28938	YOKE	A105
24	1	58113	31555	YOKE NUT	A582 TYPE 416

NOTE:
PHOSPHATE PER RMP61012.
VALVE TO BE TESTED PER MSS-SP-61 PER RMPVFLT005

X.XX Inches
[XX,X] MM

WEIGHT	47.8 LBS	21.67 Kg
Cv FACTOR		57.8

CNS	59320
REV	05
BY	R.Jackson
DATE	11-4-2005

DWN BY	R.Jackson
CHK BY	G.HAMILTON
RVD BY	
DATE	2-20-92

SERIES No:	SW1510-08	
ITEM No:	201850	
RATING: 4225 PSI • 100 F	SPECS: ASME B16.34 LTD	
BODY A105	SEAT INTG HF	DISC CC / STEM 13CR

FLOWSERVE Vogt Valves
SULPHUR SPRINGS, TEXAS, USA

1 1/2 'Y' PATTERN GLOBE VALVE -
FORGED STEEL - OS&Y - SEAL WELD BONNET-
INTEGRAL SEAT-BODY GUIDED DISC-
SOCKET WELD ENDS -CLASS 1690 LTD

57488-2

57489