






ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	1	59061	60689	1/4 X 1 3/8 DOWEL PIN	18-8 SS
2	2	58414		2 SW PROTECTOR	POLYETHYLENE
3	1	20434	59532	BODY	A105
4	1	30166	35493	BONNET	A105
5	1	55017	45706E	GASKET	304/GRAFOIL
6	4	50060	45417F	HEX HD BOLT	A193 GR B7
7	1	41358	28297	NAME PLATE	ALUMINUM
8	1	32123	40532	SEAT RING	A182 T316L HF
9	1	32413	50195	SWING CHECK DISC	A743 CA15
10	1	59013	60503	SWING CHECK SUPPORT	A351 CF8M



<-- DIRECTION OF FLOW



SERIES No:		SWS701-09	
ITEM No:		205154	
RATING: 1975 PSI • 100 F		SPECS: ASME B16.34	
BODY A105		SEAT 316 HF	DISC 13CR TRIM 316

FLOWERVE Vogt Valves	
SULPHUR SPRINGS, TEXAS, USA	
2 SWING CHECK VALVE - FORGED STEEL-BOLTED BONNET-SPIRAL WOUND GASKET JOINT-RENEWABLE SEAT SOCKET WELD ENDS -CLASS 800	
60710-2	

NOTE:
PRESS SEATS PER RMPVFSP024
VALVE TO BE TESTED PER API-598 PER RMPVFLT005

X.XX Inches [XX,X] MM		
WEIGHT	16.5 LBS	7.51 Kg
Cv FACTOR	81.9	

CNS	57747	DWN BY	R.JACKSON
REV	00	CHK BY	G.HAMILTON
BY	R.Jackson	RVD BY	
DATE	3-3-2004	DATE	9-19-2001