

Lovibond® Water Testing Tintometer® Group



MD50 Chlorine Colorimeter, LR/HR

Single Parameter Colorimeter for Water Quality Analysis



- EPA Compliant methodology for reporting purposes
- Rubberized side panels increase the durability of the instrument
- IP67 waterproof rating
- Easy data storage and transfer

Part Number: 280106

The MD50 has several key features that make it a favorite among users.

Robust Design

The MD50 is built to last. Its rugged industrial design, complete with rubber-protected sides and an IP67 rating, ensures unmatched durability and reliability even in demanding environments.

Accurate, Reproducible Results

The innovative optical system of the MD50 delivers exceptional accuracy and speed, ensuring precise readings in record time.

Factory Programmed Methods

All MD50 instruments come with pre-programmed methods for different types of reagents. Simply select the test you need, prepare your sample, and test! To simplify test selection, you can choose the reagent type from the settings and display only your desired methods in the methods list.

User Calibration and User defined Method

A one-point calibration is possible with the MD50. The instrument automatically saves the calibration protocol in the logs along with the calibration factor. All user-calibrated methods are displayed with a calibration icon on the screen. Can't find the method you need? The MD50 also allows you to program a user-defined method using PC software.

One-Time-Zero Function

Save time by zeroing the instrument once for each sample. When testing a new sample, zero the instrument once and all subsequent tests of that sample do not require re-zeroing. You can also activate or deactivate the OTZ function for all methods in the settings.

Automatic Data Storage

The MD50 automatically stores the last 100 readings and protocols with a time and date stamp. Results remain in storage even during a battery exchange.

Data Transfer

The MD50 offers smooth and effortless data transfer. You can transfer data to the AquaLX® app via NFC or use a USB cable to transfer

data to PC software. Data can also be exported in CSV format for programs like Excel.

Ergonomic Design

Whether you're using the MD50 in the field or in the lab, its design makes it easy to handle and view the display. In the field, the compact size and side protections ensure a firm grip during use. In the lab, rubber feet on the bottom of the housing eliminate the need for two-handed operation or chasing your instrument around the workbench.

GLP Compliance

To ensure data quality and integrity, the MD50 creates and saves a protocol for each change made during operation.

2-year Warranty

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Pool Domestic | Pool Public | Pool Services | Power and Energy

Application

Boiler Water | Cooling Water | Disinfection Control | Drinking Water Treatment | Pool Water Control | Raw Water Treatment | Waste Water Treatment

MD50 Chlorine Colorimeter, LR/HR

The MD50 Chlorine LR/HR Colorimeter combines a simple user interface with advanced optics to deliver the accurate and reliable results municipal and industrial users require - and packs a lot of features into a rugged, hand-held instrument. Able to perform up to 5,000 tests on a single set of batteries, this instrument automatically logs the last 100 results with time and date stamp and it's now easier than ever to transfer your results from your instrument to a smart device using the AquaLX mobile App.

This instrument utilizes the DPD method to measure two ranges of Free and Total Chlorine: 0.02 - 2 mg/l and 0.1 - 10 mg/l.

Measuring Range

Test Name	Measuring Range	Chemical Method
Chlorine HR 2 PP	0.1 - 10 mg/L Cl ₂	DPD
Chlorine PP	0.02 - 2 mg/L Cl ₂ ^{a)}	DPD

Technical Data

Optics	LED, spectrometer sensor, interference filter (selected variants only)
Light Source	LED
Wavelength	530 nm
Photometric Range	0 - 3 Abs
Photometric Accuracy	3 % FS (T = 20 °C – 25 °C)
Suitable Vials	Round Cuvettes 13 mm Round Cuvettes 16 mm Round Cuvettes 24 mm
Display	Backlit LCD
Interfaces	USB-C NFC (Near Field Communication)
Data Transfer Format	.csv
Operation	Foil keypad
Programmability	yes with PC software
Calibration	Factory and user adjustment - return to factory adjustment possible at any time
Updates	Firmware and methods update
Internal Storage	Internal ring memory for 100 data records
Battery Life Time	approx. 5000 measurements (without backlight)
Portability	Portable
Degree of Pollution	2
Maximum altitude above sea level	3500 m
Compliance	CE
Languages Full User Manual	English, German, Spanish, French, Portuguese, Italian, Dutch, Turkish, Chinese
Dimensions	6.1 x 2.99 x 1.77"

Delivery Scope

- 1 Instrument in Carrying case
- 100 Chlorine Free Powder Packs
- 100 Chlorine Total Powder Packs
- 2 batteries (AA)
- 3 round cuvettes (glass) with lid and Sealing rings
- 1 Screwdriver
- 3 Stirring rods
- 1 Syringe 10 mL
- 1 Cleaning brush
- 1 USB-C to USB-A cable
- 1 Instruction manual
- 1 Certificate (COC)
- 1 Warranty information

Title	Part Number
Water Sampler & 250 mL Bottle	170500
Round cuvette 24 mm ø, set of 12	197620
Sealing ring for round vials 24 mm ø, set of 12	197626
Round cuvette 24 mm ø, set of 5	197629
Cleaning cloth	197635
Mixing cylinder, 25 ml	19802650
USB-C cable 1 m, USB-C to A	19820-081
Reference Standard Kit Chlorine - 0.2 and 1.0 mg/l (MD50)	275620
Reference Standard Kit Chlorine - 0.5 and 2.0 mg/l (MD50)	275621
Reference Standard Kit Chlorine - 1.0 and 4.0 mg/l (MD50)	275622
Stirring rod, 13 cm length	364100
Stirring rod, 10 cm length	364109
Box with 10 plastic stirring rods	364120
Box with 10 plastic stirring rods	364130
250 mL bottle with cap	375072
Brush, 11 cm length	380230
Measuring beaker, 100ml	384801
Cuvette stand for 6 round cuvettes Ø 24 mm	418951
Plastic funnel with handle (white)	471007
ValidCheck Chlorine 1,5 mg/l	48105510

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care: +86 021 69910081
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebu Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain