STEEL PIPE CLAMPS



G

Fig. 261

Extension Pipe or Riser Clamp

Size Range: 3/4" through 24" Material: Carbon steel

Finish: ☐ Plain, ☐ Galvanized or ☐ Epoxy coated

Service: For support of stationary steel pipe risers, cast iron pipe or conduit. This product is not intended for use with hanger rods.

For this application refer to Fig. 40 Riser Clamp, page 31.

Maximum Temperature: Plain 650° F, Galvanized and Epoxy 450° F **Approvals:** Complies with Federal Specification A-A-1192A (Type 8) *WW-H-171-E (Type 8)*, ANSI/MSS SP-69 and MSS SP-58 (Type 8).

UL, ULC Listed (Sizes 1 1/2" - 8").

Installation: Clamp is fitted and bolted preferably below a coupling or welded lugs on steel pipe. Bolt torques should be per industry standards (see page 208). Clamp is designed for standard steel pipe O.D. and this must be considered in sizing the riser for other types of piping.

Ordering: Specify pipe size, figure number, name and finish.




FIG. 261: LOADS (LBS) • WEIGHT (LBS) • DIMENSIONS (IN) • TORQUE (FT-LBS)								
Pipe Size	Max Load	Weight	L	G	В	С	Bolt Diameter	Torque Values
1/2	45	1.1	87/8	1	27/8	3/8	3/8	21
3/4	220	1.1			27/8			
1		1.1			31//8			
11/4	250	1.6	10		31/2			
1 ½		1.6	101/4		37/8			
2	300	1.7	1074		41/4	1/2	7/16	32
21/2	400	1.9	111/4		43/4			
3	500	1.9	113/8		5½			
31/2	600	2.3	107/		61/2	- 1/2	1/2	46
4	750	2.4	127/8		7			
5	1,500	3.6	13¾		8	/2	/2	40
6	1,600	4.0	143/4	1½	9			
8	0.500	7.6	18½		12	- - 5/8	5/8	100
10	2,500	11.1	201/4	2	13¾			
12	2,700	16.5	223/4		15¾			
14		17.7	24		171/4			
16		30.4	26		19¾			
18	2,900	33.8	28	2½	21¾	3/4	3/4	150
20		35.0	30		23¾			
24	3,200	82.0	36¾	3	30	1	7/8	190

PROJECT INFORMATION	APPROVAL STAMP
Project:	☐ Approved
Address:	Approved as noted
Contractor:	☐ Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	