CertainTeed E

Specification Sheet

ToughGard® T Textile Duct Liner

1. PRODUCT NAME

ToughGard® T Textile Duct Liner

2. MANUFACTURER

CertainTeed Corporation P.O. Box 860 Valley Forge, PA 19482-0105 Phone: 610-341-7000

800-233-8990 Fax: 610-341-7571

Website: www.certainteed.com/

insulation

3. PRODUCT DESCRIPTION

Basic Use: ToughGard T Duct Liner is used primarily as an acoustical liner in HVAC sheet metal ducts to absorb unwanted crosstalk, equipment and air rush noise.

This product can be used in most types of comfort heating and cooling duct systems, operating at velocities up to 6,000 fpm (30.5 m/s) and temperatures to 250°F (121°C).

Benefits: ToughGard T Duct Liner is more water repellent than standard duct liners. This product is durable, abuse resistant and easy to clean. In addition, ToughGard T Duct Liner provides excellent thermal properties, exhibits low air flow resistance and meets all applicable fire resistance standards and building code requirements. This product has a factory-applied edge coating that ensures sealing of the transverse edges as per SMACNA and NAIMA Installation Standards. The product can be precision cut using both manual and automatic cutting equipment.

Composition and Materials: Composed primarily of long, textile-type glass fibers (with an average of 75% recycled content) firmly bonded together with a thermosetting resin overlaid with an extremely tough and durable fire-resistant, black composite surface on the air stream side. The airstream surface contains an EPA registered antimicrobial agent in order to reduce the potential of microbial growth that may affect this product. The antimicrobial properties are intended to only protect this product.

Limitations: Insulation should be kept clean and dry during shipping, storage, installation and system operation.

Sizes: See the table below for available sizes. Contact CertainTeed for availability and minimum order quantities.

4. TECHNICAL DATA

Applicable Standards:


- Model Building Codes:
 - ICC
- California Title 24
- Material Standards
 - (ASTM C1071)
 - (CAN/CGSB-51.11-92)
- Fire Safety Standards:
 - (NFPA 90A, NFPA 90B)

Fire Resistance:

- Fire Hazard Classification:
 - (UL 723, ASTM E84, NFPA 255)
- (CAN/ULC-S102-M88) Max. Flame Spread Index: 25 Max Smoke Developed Index: 50
- Limited Combustible: (NFPA 259)
 - < 3,500 Btu/lb

Physical/Chemical Properties:

- Thermal Performance:
- See table on other side.



- Acoustical Performance:
- See table on other side.
- Operating Limits:
 - Temperature: (ASTM C411) Max. 250°F (121°C)
 - Air Velocity: (ASTM C1071, UL181)
 Max. 6,000 fpm (30.5 m/s)
- Water Vapor Sorption: (ASTM C1104)
 -≤ 3% by weight
- Corrosiveness: (ASTM C665)
 - Pass
- Bacteria Resistance: (ASTM G22)
 - No Growth
- Fungi Resistance: (ASTM C1338 & ASTM G21)
 - Pass; No Growth
- Water Repellency Rating
 - ≥ 4 (INDA IST 80.6-92)

STANDARD SIZES											
pe	Nominal	Thickness	Le	ngth	Width						
ASTM	in.	mm	ft.	m	in.	mm					
Ι	1	25	50 & 100	15.2 & 30.5		610 to 1829 in 6 mm increments					
	1 ¹ / ₂	38	100	30.5							
	2	51	50	15.2							
	1/2	13	100	30.5	24 to 72						
	1	25	50 & 100	15.2 & 30.5	in 1/4" increments*						
	1/2	13	100	30.5							
	1	25	50 & 100	15.2 & 30.5							
	ASTM	ASTM in. 1 11/2 2 1/2 1 1 1/2	Pe Nominal Thickness ASTM in. mm 1 25 11/2 38 2 51 11/2 13 1 25 11/2 13	Pe Nominal Thickness Leader	Nominal Thickness Length m	Nominal Thickness Length Wi					

1) Classification per ASTM C107: Type I is roll form; Type II is sheet form

*Not all widths between 24" and 72" are standard. Please contact CertainTeed for the standard sizes.

*Made-To-Order sizes are available and subject to an upcharge, additional lead time and minimum quantities.

Quality Assurance: Many of CertainTeed's insulation manufacturing plants are registered to ISO 9001-2000 standards.

5. INSTALLATION

All duct liner products shall be installed in accordance with the requirements of NAIMA Fibrous Glass Duct Liner standard, or SMACNA HVAC Duct Construction standards and the project specification.

The products can be precision cut using both manual and automatic cutting equipment. The liner shall be cut and fitted to ensure all joints are neatly and tightly butted with no interruptions or gaps.

All duct liner products shall be adhered to the sheet metal ductwork using an adhesive meeting the requirements of ASTM C916. The adhesive film coverage shall be a minimum 90% of the metal surface. Secure the duct liner to the sheet metal ductwork using mechanical fasteners (impact-driven or weld-secured). These fasteners vary in length and type. Mechanical fasteners of the specified type and length shall be used, ensuring no greater than 10% compression of the liner thickness. Maximum fastener spacing shall be in accordance with NAIMA or SMACNA standards.

ToughGard T Duct Liner provides clean "buttered" transverse edges. However, some circumstances will require the use of adhesive to butter raw exposed liner edges. Final job site buttering may be required to coat duct cut-ins and/or minor installation damage.

ToughGard T Duct Liner fabricated duct systems shall be kept clean and dry from the point of fabrication through job site installation. Special precautions at the job site may be necessary to accomplish this. The installed lined ductwork shall be protected to avoid contamination by water and dirt.

An HVAC system commissioning program should be considered to ensure proper start up and purging of the duct system.

Design Considerations:

- Butter all raw exposed edges.
- High, in-duct air turbulence areas may require special procedures, i.e. perforated inner metal liner, etc.
- Metal nosings shall be securely installed over transversely oriented liner edges facing air stream at fan discharge and at any interval of lined duct preceded by unlined duct.

6. AVAILABILITY AND COST

Manufactured and sold throughout the United States. For availability and cost contact your local distributor, or call CertainTeed Sales Support Group in Valley Forge, PA at 800-233-8990.

INSERTION LOSS, dB per ft of Lined Duct												
P/A, ft/ft²	1" Liner frequence Hz 125	cies,			er 2000	4000	frequ	er Octav encies, 25 250		d cente 1000		4000
8	0.6	1.5	2.7	5.8	7.4	4.3	0.8	2.9	4.9	7.2	7.4	4.3
6	0.5	1.2	2.3	5.0	5.8	3.6	0.6	2.3	4.2	6.2	5.8	3.6
4	0.4	0.8	1.9	4.0	4.1	2.8	0.5	1.6	3.5	5.0	4.1	2.8
2	0.2	0.5	1.4	2.8	2.2	1.8	0.3	0.8	2.3	3.3	2.0	1.7
1	0.1	0.3	1.0	2.0	1.2	1.2	0.2	0.5	1.8	2.3	1.1	1.1


Duct Liner Insertions Loss—Data extracted from ASHRAE Handbook, HVAC Applications, Chapter 46, 1999. P/A = duct perimeter, ft/duct cross sectional area (ft²). Example: 12" x 12", P/A = 4 (1/ft).


ACOUSTICAL PERFORMANCE												
	Product	t	Sound	Sound Absorption Coefficients @ Octave Frequencies (Hz)								
Type	Nomimal Thickness		125	250	500	1000	2000	4000	NRC			
Type	in.	mm	125	250	500	1000	2000	4000	NKC			
	1	25	0.14	0.29	0.55	0.77	0.94	0.94	0.65			
150	1 ¹ /2	38	0.16	0.47	0.77	0.96	1.04	1.00	0.80			
	2	51	0.23	0.62	1.01	1.04	1.00	1.01	0.90			
200	1/2	13	0.06	0.15	0.33	0.56	0.76	0.91	0.45			
	1	25	0.10	0.33	0.65	0.86	0.94	0.96	0.70			
	1 ½	38	0.16	0.47	0.77	0.96	1.04	1.00	0.80			
	2	51	0.24	0.57	0.90	0.95	0.95	0.96	0.85			
300	1/2	13	0.06	0.15	0.33	0.56	0.76	0.91	0.45			
	1	25	0.10	0.33	0.65	0.86	0.94	0.96	0.70			
	1 ¹ /2	38	0.20	0.46	0.82	0.94	0.95	0.91	0.80			
	2	51	0.27	0.72	1.04	1.02	0.96	0.92	0.95			


THERMAL PERFORMANCE										
Product			K-Va	lue	C-V	alue	R-Value			
Туре	Nominal Thickness*		Btu•in W		Btu W		h•ft.2•°F	m ² •°C		
	in.	mm	h•ft. ² •°F	m•°C	h•ft.²•°F	m ² •°C	Btu	W		
	1	25	0.26	0.038	0.25	1.42	4.0	0.70		
150	1 ¹ /2	38	0.27	0.039	0.17	0.95	6.0	1.06		
	2	51	0.26	0.038	0.13	0.71	8.0	1.41		
	1/2	13	0.25	0.036	0.5	2.84	2.0	0.35		
200	1	25			0.24	1.35	4.2	0.74		
200	11/2	38			0.17	0.95	6.0	1.06		
	2	51			0.13	0.71	8.0	1.41		
	1/2	13		0.035	0.48	2.73	2.1	0.37		
300	1	25	0.24		0.23	1.30	4.4	0.77		
300	11/2	38			0.16	0.91	6.3	1.10		
	2	51			0.12	0.68	8.3	1.47		

Thermal conductance (C) and resistance (R) values are derived from the material thermal conductivity (k) value. Tested in accordance with ASTM C518 and/or ASTM C177 at 75° F (24° C) mean temperature.

*Actual finished thicknesses are 1.05" thick (nominal 1.0"), actual 1.6" (nominal 1.5", Type 150), actual 2.1" (nominal 2", Type 150).







7. WARRANTY

Refer to CertainTeed's Limited One-year Warranty for ToughGard T Fiber Glass Duct Liner (30-29-047).

8. MAINTENANCE


An inspection and preventative maintenance program for the HVAC system is recommended to ensure optimum performance. Use NAIMA guidelines for duct cleaning methods and procedures.

9. TECHNICAL SERVICES

Technical assistance can be obtained either from the local CertainTeed sales representative, or by calling CertainTeed Sales Support Group in Valley Forge, PA at 800-233-8990.

10. FILING SYSTEMS

- Sweet's Engineering & Retrofit Files
- CertainTeed Pub. No. 30-36-004
- Additional product information available upon request.













ASK ABOUT OUR OTHER CERTAINTEED PRODUCTS AND SYSTEMS:

EXTERIOR: ROOFING • SIDING • WINDOWS • FENCE • RAILING • TRIM • DECKING • FOUNDATIONS • PIPE **INTERIOR:** INSULATION • GYPSUM • CEILINGS

CertainTeed Corporation P.O. Box 860 Valley Forge, PA 19482 Professional: 800-233-8990 Consumer: 800-782-8777 www.certainteed.com/insulation

