

DURACELL®



COPPERTOP

MN1604




Size: 9V (6LR61)

Alkaline-Manganese Dioxide Battery

Zn/MnO₂



| | |
|-----------------------------|---|
| Nominal voltage | 9 V |
| Impedance | 1,700 m-ohm @ 1 kHz |
| Typical weight | 45 g (1.6 oz) |
| Typical volume | 22.8 cm ³ (1.4 in ³) |
| Terminals | Miniature snap |
| Storage temperature range | 5°C to 30°C (41°F to 86°F) |
| Operating temperature range | -20°C to 54°C (-4°F to 130°F) |
| Designation | ANSI: 1604A IEC: 6LR61 |







DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.



Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

