



# Residential Gas Water Heaters

## ProMax<sup>®</sup> + PLUS HIGH EFFICIENCY

### FEATURES

#### INTELLIGENT CONTROL LOGIC

The internal microprocessor provides enhanced operating parameters and tighter differentials for precise sensing and faster heating response to optimize performance.

#### SELF-POWERED ELECTRONIC GAS VALVE

Uses a thermopile to generate the power needed to operate the electronic gas control without requiring an external power source.

#### DIAGNOSTICS

The electronic gas control incorporates an LED status indicator that monitors system operation & service diagnostics.

#### DYNACLEAN™ DIFFUSER DIP TUBE

Helps reduce lime and sediment buildup, maximizes hot water output. Made from long-lasting PEX cross-linked polymer.

#### GREEN CHOICE® GAS BURNER

Patented "Eco-Friendly" design reduces NOx emissions by up to 33% and complies with requirements for low NOx emissions.

#### "ENVIRONMENTALLY-FRIENDLY" 2 INCH NON-CFC FOAM INSULATION IMPROVES EFFICIENCY

#### COREGARD™ ANODE ROD

An A. O. Smith exclusive. Aluminum anode has stainless steel core, protects tank against corrosion.

#### PUSH-BUTTON PIEZO IGNITOR

Makes lighting pilot fast and easy with one-hand push-button spark ignition.

#### DURABLE, TAMPER-RESISTANT BRASS DRAIN VALVE

#### BLUE DIAMOND® GLASS COATING

Provides superior corrosion resistance to industry-standard glass lining.

#### CSA CERTIFIED AND ASME RATED T&P RELIEF VALVE

Top-mounted T&P relief valve available as option on all models.

#### CODE COMPLIANCE

UBC, CEC, SBCC, HUD and BOCA National Codes. Meets the thermal efficiency and standby loss requirements of the U.S. Department of Energy and current edition of ASHRAE/IESNA 90.1 and meets the Federal Energy Efficiency Standards effective January 20, 2004, according to the National Appliance Energy Conservation Act (NAECA) of 1992.

#### DESIGN-CERTIFIED BY CSA INTERNATIONAL

According to ANSI Z21.10.1 - CSA 4.1 Standards governing storage-type water heaters.

#### FLAMMABLE VAPOR IGNITION RESISTANT COMPLIANT DESIGN

See other side.

#### 6-YEAR LIMITED TANK AND PARTS WARRANTY

For complete information, consult written warranty or A. O. Smith Water Products Company.





# Residential Gas Water Heaters

## ProMax<sup>®</sup> + PLUS HIGH EFFICIENCY


MODEL NUMBER	SERIES	FIRST HOUR RATING (GAL)	ENERGY FACTOR	GALLON CAPACITY	BTU INPUT PER HOUR NAT/LP	RECOVERY 90°F RISE GALLONS PER HOUR	FOAM THICKNESS (INCHES)	DIMENSIONS IN INCHES						DRAFT HOOD OUTLET	APPROXIMATE SHIPPING WEIGHT (LBS)
								A	B	C	D	E	F		
<b>TALL MODELS</b>															
GVR-30	300/301	67	.62	30	35,500/32,000	36	2	61-1/2	58	18	13	8	52	3 or 4	126
GVR-40	300/301	70	.62	40	40,000/36,000	41	2	61-3/4	58-1/4	20	13	8	51-3/4	3 or 4	150
GVR-50	300/301	88	.62	50	40,000/37,000	41	2	61	57-1/4	22	13	8	50-1/4	3 or 4	165
<b>SHORT MODELS</b>															
GVRL-30	401	60	.61	30	32,000	36	2	50	46-3/8	20	13-1/2	8	40	3 or 4	123
GVRL-40	300/301	67	.62	40	40,000/36,000	41	2	51-1/2	47-3/4	22	13	8	41	3 or 4	147

Recovery capacity based on actual performance tests.  
 Water Connections – 3/4" on all models.  
 For 10-Year Tank and 6-Year Parts Warranty, change "G" to "X" in Model Number (example: XVR-40).  
 Heat Trap Nipples are factory-installed on all models.  
 GVRL-30 is only available in LP Gas.



### Flammable Vapor Ignition Resistant (FVIR) Water Heaters

A. O. Smith FVIR design meets or exceeds the American National Standards Institute standards (ANSI Z21.10.1 - CSA 4.1) that deal with the accidental or unintended ignition of flammable vapors, such as those emitted by gasoline.

Feature a sealed combustion chamber with air intake filter and a flame arrestor built into the water heater base. In addition, a thermal cutoff (TCO) device, is designed to shut off gas flow to the burner and pilot if poor combustion is detected.



If flammable vapors accidentally enter the combustion chamber, the arrestor is designed so flames burn off the top surface and cannot escape down through the arrestor.



\*Location for optional top-mounted T&P Valve if ordered from factory.

Maximum Hydrostatic Working Pressure: 150 PSI

- A. Industry standard Thermopile
- B. Large View Port for easy burner inspection
- C. 360° Combustion Air Filter
- D. Thermal Cutoff (TCO) with manual reset

For Technical Information and Automated Fax Service, call 800-527-1953. A. O. Smith Corporation reserves the right to make product changes or improvements without prior notice.