


AS 51

EG Other _____

RIGHT ANGLE PIPE OR CONDUIT CLAMP



Size	A Dia.	B	Wt/100 pcs
3/8"	5/16"	15/16"	25
1/2"	5/16"	13/16"	41
3/4"	5/16"	17/16"	42
1"	5/16"	11/16"	47
1 1/4"	5/16"	2"	54
1 1/2"	5/16"	2 5/16"	57


Size	A Dia.	B	Wt/100 pcs
2"	3/8"	2 3/16"	85
2 1/2"	3/8"	3 3/8"	106
3"	3/8"	4 1/8"	110
3 1/2"	3/8"	4 5/8"	128
4"	3/8"	5 1/8"	140

Std Pkg: 50 · Wt/100 pcs: See chart above.

AS 270

EG Other _____

CONDUIT CLAMP



A	Std Pkg	Wt/100 pcs
3/8" - 1/2"	50	6
3/4"	50	8
1"	50	9
1 1/4"	25	11
1 1/2"	25	19
2"	25	27

Std Pkg & Wt/100 pcs: See chart above.

AS 815

EG Other _____

(6" TO 16" PIPE) DOUBLE ROLLER PIPE SUPPORT

Order Nuts and Bolts Separately.



Load Rating: 1500 lbs.

For "A" Dimension Recommendations, See Chart On Page 87.

Std Pkg: 5 Pr. · Wt/100 pcs: 680 lbs.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium

PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	