## Flat Hanger Screws **HBT Installation Tool - PC 4920**



• Flat Hanger Screws • Flat Hanger Tool w/ Safety Sleeve

<ul> <li>Tool Not Included</li> </ul>	<ul> <li>Heavy Duty Steel Construction</li> </ul>
• TK - With Drill Pt.	<ul> <li>Installs Hanger Screws Quickly</li> </ul>

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT	
631 631TK	18135 18136	1/4 x 3" 1/4 x 2"	100 100	1000 1000	2.38# 2.38#	C C	
HBT	28950	Installation Tool	1	6	0.11#	Ea	


## **Hanger Bolts** E-Z Hanger Bolt Tool - PC 4940

Lag/Machine Screw Threads

28953

28956

- Heavy Duty Steel Construction
- Threads On For Quick Installation
- Improved: With Ball Bearing Release To Reduce Hanger Bolt Lockup



## **Drive Screws** PC 4960

EZ14

EZ38

Hanger Bolts

Tool Not Included

- Multi-purpose concrete drive-in fastener. Steel
- Hammer Drive

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
216	18120	2" x 16	100	1000	2.66#	С

## **Fluorescent Fixture Hangers** PC 4970

- · Top-Mount or Side Mount
- Fluorescent Fixture Hangers
- · Galvanized Steel
- For Use With 2, 3 or 4 Light Fixtures

6

0.11#

1.17#

Fluorescent Fixture Hangers are manufactured from
10 gauge Galvanized Steel and are typically used
with S hooks and jack chain.
•

CAT NO	UPC		DESCRIPTION	STD	MSTR	WT/STD	UNIT	
629	18125	Side-Mount	10 GA	100	500	6.18#	С	
630	18130	Top-Mount	10 GA	100	500	6.18#	С	



Ea

Ea



629

630