


Mirafi® PET 1000/100



Mirafi® PET 1000/100 geotextile is composed of high tenacity polyester multifilament yarns which are woven into a stable network such that the yarns retain their relative position. Mirafi® PET 1000/100 geotextile is inert to biological degradation and resistant to naturally encountered chemicals, alkalis, and acids.

Mechanical Properties	Test Method	Unit	Minimum Average Roll Value	
			MD	CD
Tensile Strength (at ultimate)	ASTM D4595	lbs/ft (kN/m)	68522 (1000)	6852 (100)
Creep Reduced Strength	ASTM D5262	lbs/ft (kN/m)	41113 (600) ²	
Long Term Design Strength ¹	GRI-GT7	lbs/ft (kN/m)	33980 (496) ²	
Tensile Strength in Machine Direction (at 5% strain)	ASTM D4595	lbs/ft (kN/m)	27409 (400)	
Carboxyl End Group	GRI-GG7	mmol/kg	< 30	
Molecular Weight	GRI-GG8	--	> 25000	

¹ Long Term Allowable Design values are for sand, silt and clay.

² Machine Direction; based on third party testing.

Physical Properties	Unit	Typical Value
Roll Dimensions (width x length)	ft (m)	16.4 x 328 (5 x 100)
Roll Area	yd ² (m ²)	598 (500)
Estimated Roll Weight	lbs (kg)	2519 (1143)

Disclaimer: TenCate assumes no liability for the accuracy or completeness of this information or for the ultimate use by the purchaser. TenCate disclaims any and all express, implied, or statutory standards, warranties or guarantees, including without limitation any implied warranty as to merchantability or fitness for a particular purpose or arising from a course of dealing or usage of trade as to any equipment, materials, or information furnished herewith. This document should not be construed as engineering advice.

Mirafi® is a registered trademark of Nicolon Corporation.

Copyright © 2014 Nicolon Corporation. All Rights Reserved.