


### GENERAL DESCRIPTION:

Complete commercial shower system includes: an R120SS pressure balance valve and trim, a wall supply with 1/2" NPT female inlet and 1/2" NPSM male outlet, a 59" (1500mm) metal shower hose, vacuum breaker, a 3-function hand shower with pause feature, and a 36" slide-grab bar.

Valve features a cast brass body, washerless 47mm ceramic disc valve cartridge with volume and temperature control, back-to-back capability, integrated check valves and hot limit safety stop. Pressure balancing cartridge maintains constant output temperature in response to changes in relative hot and cold supply pressure. One-half inch direct sweat inlets and outlets. With screwdriver stops. Rough-in plaster guard designed for use as thin-wall mounting adapter. Durable metal handle. 3-function hand shower with pause feature and 2.5gpm/9.5L/min. flow restrictor. Slide-Grab Bar features an adjustable shower holder which can be set at any height or position along the bar and angle up to 45°.



### SUGGESTED SPECIFICATION:

Shower system shall feature a wall supply with 1/2" NPT female inlets and 1/2" NPSM male outlet, 59" metal hose, vacuum breaker, 2.5 rpm/9.5L/min. 3-function hand shower with pause feature and a 36" slide-grab bar. Pressure Balance valve shall feature a cast brass body. Shall feature ceramic disc valve cartridge which controls water temperature and volume. Shall also feature hot limit safety stop. Fitting shall be American Standard Model # 1662SG.221.002.

### MODEL NUMBER:

#### 1662SG.221 Commercial Shower System Kit

Includes:

• Shower Valve with SS	R120SS
• Colony Soft Valve Only Trim	T675.500.002
• 3-F Hand Shower with Pause Feature	1660.767.002
• In-Line Vacuum Breaker	1660.400.002
• Metal Hose	8888.035.002
• Wall Supply	8888.037.002
• 36" Slide-Grab Bar	1662.236.002

### PRODUCT FEATURES:

#### VALVE:

**Cast Brass Valve Body:** Durable.

**Ceramic Disc Valve Cartridge:** Assures a lifetime of drip-free performance. Allows control over water temperature and volume.

**Pressure Balancing Valve Cartridge:** Maintains constant output temperature in response to changes in hot and cold supply pressure. Diaphragm system with integrated check valves engineered to eliminate cross flow.

**Back-to-Back Capability:** Hot and cold can be reversed quickly and easily.

**Adjustable Hot Limit Safety Stop:** Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding.

#### Integral Plaster Guard and Mounting Plate:

Protects valve during installation and serves as a mounting plate for thin-wall installations.

#### PERSONAL SHOWER:

**ADA-Compliant:** Non-positive shut-off button on handle reduces flow to a trickle.

#### SLIDE-GRAB BAR:

**Stronger Than Standard Slide Bars:** 1-1/2" diameter stainless steel bar meets ANSI standard 250 lb. pull test. Chrome-plated hand shower holder with ADA compliant lever handle.

### CODES AND STANDARDS

Install as required to comply with local code requirements.

ASME A112.18.1  
ASSE 1016  
CSA B 125  
ANSI A117.1

Product Number	Description	Finish
		Polished Chrome
		002
1662SG.221	Commercial Shower System Kit. Contains pressure balance valve with volume and temperature control, trim kit, 3-function hand shower with pause feature, metal hose, vacuum breaker, wall supply and 36" slide-grab bar. 2.5gpm/9.5L/min.	

