

# Wall Mounted High-SEER 9, 12 and 15,000 BTU Systems

Systems 9RLS3, 12RLS3, 15RLS3



Up to 33.0 SEER



**Indoor Models**  
ASU9RLS3  
ASU12RLS3  
ASU15RLS3



**Outdoor Models**  
AOU9RLS3  
AOU12RLS3  
AOU15RLS3

## Energy Efficient

	9RLS3	12RLS3	15RLS3
SEER	33.0	29.3	25.3
EER	18.0	15.2	13.9
HSPF	14.2	14.0	13.4

## World's Most Efficient Heat Pump



All systems feature high efficiencies and are **ENERGY STAR® Most Efficient 2015 Qualified**, meaning lower utility bills for home and business owners.

## Rebates

To encourage customers to buy energy efficient products, many states and/or local utility companies offer significant rebates for the purchase of a ductless mini-split system. Go to Fujitsu's web site to search for local rebates, consumer loans and utility bill discounts. We provide a listing of rebates and offerings on qualifying Fujitsu mini-splits by state. [www.fujitsugeneral.com/utility\\_rebates.htm](http://www.fujitsugeneral.com/utility_rebates.htm)



## ESP Energy Saving Program

ESP knows how to save you money even when you forget. If you leave the room without turning the unit off, ESP knows that you left and 20 minutes later, set temperature is increased by 4°F when cooling and reduced by 8°F when heating. When you come back to the room, it returns to previous operating mode. This prevents wasteful operation to save energy without you having to think about it.



## Power Diffuser




A power diffuser operates automatically in either heating or cooling mode to optimally control the airflow. A comfortable space is quickly achieved.



**Cooling**  
During cooling mode, far reaching horizontal airflow quickly creates a comfortable space throughout the entire room.



**Heating**  
During heating mode, vertical airflow provides comfortable floor level heating.



## Standard Features

Wireless Remote Control	Economy Mode
Apple Catechin Filter	Energy Saving Program
Ion Deodorizing Filter	Quiet Mode (Indoor)
Sleep Timer	Low Noise Mode
24 Hour Timer	Auto Restart/Reset
Weekly Timer	Auto Changeover
Dry Mode	Low Ambient Cooling
Auto Louver: 4-Way	Cold Prevention
Auto Mode	Remote Temp. Sensor*
Powerful Operation Mode	3 <sup>rd</sup> Party Device Control*


\* Available only with optional wired remote controller and optional interface kit.  
+ Available only with optional interface kit. Operation monitoring and On/Off control only.

## Optional Accessories


- Wired Remote Controller: UTY-RVNUM  
*Backlit and includes room temperature*
- Wired Remote Controller: UTY-RNNUM
- Simple Remote Controller: UTY-RSNUM
- Communication Kit: UTY-TWBXF1
- Dry Contact Wire Kit: UTY-XWZXZ5

## Dimensions Inches (mm)

### ASU9RLS3, ASU12RLS3, ASU15RLS3



### AOU9RLS3, AOU12RLS3, AOU15RLS3



The Fujitsu logo is a registered trademark of Fujitsu Limited. The Halcyon logo and name is a trademark of Fujitsu General America, Inc. ENERGY STAR is a registered trademark of the EPA and DOE. Copyright 2015 Fujitsu General America, Inc.

Proper sizing and installation of equipment is critical to achieve optimal performance. Split system air conditioners and heat pumps must be matched with appropriate coil components to meet ENERGY STAR criteria. Ask your contractor for details or visit [www.energystar.gov](http://www.energystar.gov).

Fujitsu's products are subject to continuous improvements. Fujitsu reserves the right to modify product design, specifications and information without notice and without incurring any obligations.

	9RLS3 Heat Pump	12RLS3 Heat Pump	15RLS3 Heat Pump
	LEARN MORE AT <a href="http://energystar.gov">energystar.gov</a>	LEARN MORE AT <a href="http://energystar.gov">energystar.gov</a>	LEARN MORE AT <a href="http://energystar.gov">energystar.gov</a>

Nominal Cooling <i>BTU/h</i>	9,000	12,000	14,500
Min.~Max. Cooling <i>BTU/h</i>	3,100~12,000	3,100~13,600	3,100~18,400
Nominal Heating <i>BTU/h</i>	12,000	16,000	18,000
Min.~Max. Heating <i>BTU/h</i>	3,100~22,000	3,100~22,100	3,100~23,900
HSPF <i>BTU/hW</i>	14.2	14.0	13.4
SEER <i>BTU/hW</i>	33.0	29.3	25.3
EER <i>Clg/Htg</i>	18.0	15.2	13.9
Clg. Operating Range °F(°C)	14~115 (-10~46)	14~115 (-10~46)	14~115 (-10~46)
Htg. Operating Range °F(°C)	-5~75 (-21~24)	-5~75 (-21~24)	-5~75 (-21~24)
Moisture Removal <i>Pt./h(l/h)</i>	2.6 (1.2)	2.7 (1.3)	4.0 (1.9)
Voltage/Frequency/Phase	208-230/60/1	208-230/60/1	208-230/60/1
MAX.CRT.BKR (A)	15	15	20
Air Circ. <i>C.F.M. (m<sup>3</sup>/h)</i> : Hi	489 (830)	489 (830)	547 (930)
Medium	400 (680)	400 (680)	459 (780)
Low	341 (580)	341 (580)	371 (630)
Quiet	224 (380)	224 (380)	Clg 259 (440) Htg 294 (500)
Noise Level <i>dB(A) Clg/Htg</i> : Hi	42/41	42/41	45/45
Medium	37/35	37/35	40/39
Low	32/31	32/31	34/33
Quiet	23/23	23/23	26/27
Outdoor Fan Speed <i>RPM Clg/Htg</i>	989/1,082	989/1,082	1,206/1,082
Outdoor Noise Level <i>dB(A) Clg/Htg</i>	42/47	43/47	49/50
Current <i>Rated/Max (A)</i> : Cooling	2.5/9.4	3.8/9.4	4.8/9.9
Heating	3.3/10.0	4.7/11.9	5.2/13.9
Power Use <i>Rated/Max (kw)</i> : Cooling	0.50/0.85	0.79/0.99	1.04/1.56
Heating	0.66/1.93	1.01/1.94	1.15/2.19
Fan Speeds <i>Stage</i>	4+Auto	4+Auto	4+Auto
Air Direction: <i>Horizontal</i>	Automatic	Automatic	Automatic
<i>Vertical</i>	Automatic	Automatic	Automatic
Air Filter	Washable	Washable	Washable
Connection Method	Flare	Flare	Flare
Combined Min. Lgth <i>Ft (m)</i>	10 (3)	10 (3)	10 (3)
Combined Max. Lgth <i>Ft (m)</i>	66 (20) (pre-charge: 49')	66 (20) (pre-charge: 49')	66 (20) (pre-charge: 49')
Max. Vertical Diff. <i>Ft (m)</i>	49 (15)	49 (15)	49 (15)
Conn. Pipe Diameter <i>Inch</i>	Suc.3/8 Dis.1/4	Suc.3/8 Dis.1/4	Suc.1/2 Dis.1/4
Net Weight <i>lbs. (kg)</i>	31 (14) 295	84 (38) 295	31 (14) 295
Dimensions: Height <i>Inch</i>	11-5/8	24-7/16	11-5/8
<i>mm</i>	295	620	295
Width <i>Inch</i>	37	31-1/8	37
<i>mm</i>	940	790	940
Depth <i>Inch</i>	10-5/8	11-7/16	10-5/8
<i>mm</i>	270	290	270
Refrigerant	R410A	R410A	R410A

Indoor	ASU9RLS3	Indoor	ASU12RLS3	Indoor	ASU15RLS3
Outdoor	AOU9RLS3	Outdoor	AOU12RLS3	Outdoor	AOU15RLS3

Note: Figures are based on 230 Volts.

