



**GENERAL DESCRIPTION:**

Electronic faucet with proximity operation. Vandal-resistant solid brass construction. Operates on DC (battery) or AC permanent power. Water pressure range from 20 to 125 psi. Single inlet 15" flexible stainless steel hose with 3/8" compression fitting for spout connection.

**PRODUCT FEATURES:**

**Vandal-Resistant Brass Body:** Durable - Excellent in high use applications.

**Power Options:**

- **Battery** - Lithium CR-P2 battery. Battery Life - Approx. 200,000 cycles (4 years @ 4,000 cycles per month).
- **Plug-In** - Plug-In - Universal low voltage transformer (80 - 250 VAC, 50 - 60 Hz) with 6 foot long cord. One power supply can run up to 15 faucets and/or flush valves in series.

**Easy and Flexible Installation:**

3-Hole, 4" Centerset installation. Water resistant solenoid enclosure mounts to wall.

**Integrated; Easy Service Strainer:**

Patented integrated strainer enclosed in removable debris cup protects the solenoid valve and aerator from debris. Perforated stainless steel strainer is low maintenance and can be easily accessed.

**Temperature Mixing:**

Optional thermostatic mixing valve. Mixing valve will connect directly to solenoid inlet and is housed in matching enclosure.

**Lead Free:** Faucet contains ≤ 0.25% total lead content by weighted average.

**MODEL NUMBER:**

- **DC POWERED; single inlet**
  - **6055.204** with cast spout, 0.35 GPM pressure compensating, vandal-resistant non-aerated spray. CR-P2 lithium battery included. Faucet is factory set for 7.5 second running time to deliver 0.044 gallons per cycle.
- **AC POWERED; single inlet**
  - **6056.204** with cast spout, 0.35 GPM pressure compensating, vandal-resistant non-aerated spray. Includes AC power supply (M950169-0070A). Faucet is factory set for 7.5 second running time to deliver 0.044 gallons per cycle.
- **OPTIONAL Mixing Valve**
  - **605XTMV** Thermostatic mixing valve, flex hoses 3/8" compression 20" hose length.

**RECOMMENDED SPECIFICATION**

Electronic Proximity Lavatory shall feature vandal resistant all brass body with single inlet, and in-line strainer. Shall also feature a low energy use electronically operated solenoid valve and microprocessor controlled proximity sensors. Shall meet ANSI A112.18.1 and ANSI 117.1 codes. Shall feature 0.35 gpm pressure compensating vandal-resistant non-aerated spray. Faucet is factory set for 7.5 second running time to deliver 0.044 gallons per cycle. Fitting shall be American Standard Model # 6055.204, 6056.204.

**CODES AND STANDARDS**

These products meet or exceed the following codes and standards:

- ANSI A117.1**
- ASME A112.18.1**
- CSA B 125**
- NSF 61/Section 9, Annex G**
- CALGreen**

 **MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES**

