

THIS SPACE FOR DESIGNER/ENGINEER APPROVAL

Job/Customer _____	Date _____	Contractor _____
Model Specified _____	Qty _____	Approved By _____
Designer/Engineer _____	Date _____	Contractor's PO# _____
Submitted by _____	Date _____	Other _____

1070W Series

Brass In-Line Spring Check Valve

316 Stainless Steel Spring – Celcon Poppet

Soft Seat

IPS

300 PSI

ISO 9001


Lead Free products are certified to
NSF/ANSI 61-G & NSF/ANSI 372



ITEM #	SIZE	CTN	CASE	D	L	CV Rate US gal/min
10701W	3/8"	60	240	1"	1 7/8"	2.39
10702W	1/2"	10	100	1 1/4"	2 3/16"	4.30
10703W	3/4"	7	70	1 1/2"	2 3/8"	11.90
10704W	1"	5	50	1 7/8"	2 1/2"	25.10
10705W	1 1/4"	5	40	2 1/4"	3"	42.10
10706W	1 1/2"	5	30	2 1/2"	3 1/8"	65.00
10707W	2"	2	20	3 1/8"	3 7/16"	123.60



NO.	DESCRIPTION	LEAD FREE BRASS MATERIAL
1	BODY	LEAD FREE BRASS
2	BONNET	LEAD FREE BRASS
3	CHECK MODULES	PLASTIC
4	GASKET	EPDM
5	CHECK MODULES	PLASTIC
6	SPRING	S.S.



Specifications: Designed for residential, commercial or industrial use with water, oil or gas. Threaded ends comply with ANSI B1.20.1. Valve pressure is < 1 PSIG.

Webstone
VALVE INNOVATION

Quality and Commitment Since 1954

www.webstonevalves.com P: (800) 225-9529 F: (800) 336-5133

Webstone product specifications in U.S. customary units are approximate and are provided for reference only. Webstone reserves the right to change or modify product design, construction, specifications or materials without prior notice and without incurring any obligation to make such changes and modifications on Webstone products previously or subsequently sold.

1070WSpec_10132015