
THIS SPACE FOR DESIGNER/ENGINEER APPROVAL				
Job/Customer	Date	Contractor		
Model Specified	Qty	Approved By		
Designer/Engineer	Date	Contractor's PO#		
Submitted By	Date	Other		

Hydro-Core ManifoldsFlange Right 600 WOG

ISO 9001



ITEM#	CTN/CASE	RUN	VALVE	DRAIN	UNION	FLANGE	HOSE						
		Α			В	С	D	E	F	G	Н	ı	J
FIP	FIP												
48754-0	1/6	1 1/4"	1	1/2	1	1	3/4	8 7/8	7 1/2	4	5 3/8	6 3/16	3 3/4
48764-0	1/6	1 1/2"	1	1/2	1	1	3/4	8 7/8	7 1/2	4	5 1/2	6 3/16	3 3/4
48755-0	1/6	1 1/4"	1 1/4	3/4	1 1/4	1 1/4	3/4	10	8 1/4	4 3/8	6	6 3/8	4 1/8
48765-0	1/6	1 1/2"	1 1/4	3/4	1 1/4	1 1/4	3/4	10	8 1/4	4 3/8	6	6 3/8	4 1/8
48766-0	1/4	1 1/2"	1 1/2	3/4	1 1/2	1 1/2	3/4	10 7/8	8 1/4	5	6 3/8	7 1/2	4 1/8
SWT													
58744-0	1/6	1"	1	1/2	1	1	3/4	9	7 1/2	4	5 1/2	6 3/16	3 3/4
58754-0	1/6	1 1/4"	1	1/2	1	1	3/4	8 7/8	7 1/2	4	5 1/4	6 3/16	3 3/4
58764-0	1/6	1 1/2"	1	1/2	1	1	3/4	8 7/8	7 1/2	4	5 7/16	6 3/16	3 3/4
58774-0	1/4	2"	1	1/2	1	1	3/4	9	8	4	5 7/8	6 3/16	3 3/4
58755-0	1/6	1 1/4"	1 1/4	3/4	1 1/4	1 1/4	3/4	10	8 1/4	4 3/8	5 3/4	6 3/8	4 1/8
58765-0	1/6	1 1/2"	1 1/4	3/4	1 1/4	1 1/4	3/4	10	8 1/4	4 3/8	5 7/8	6 3/8	4 1/8
58775-0	1/4	2"	1 1/4	3/4	1 1/4	1 1/4	3/4	10	8 5/8	4 3/8	6 3/8	6 3/8	4 1/8
58766-0	1/4	1 1/2"	1 1/2	3/4	1 1/2	1 1/2	3/4	10 7/8	8 1/4	5	6 1/4	7 1/2	4 1/8
58776-0	1/4	2"	1 1/2	3/4	1 1/2	1 1/2	3/4	10 7/8	8 5/8	5	6 3/4	7 1/2	4 1/8



TEMP	WOG
100	600
150	485
200	395
250	210
300	N/A
350	N/A
366	N/A


FLANGE C	KA	КВ	КС	KD
1"	1/2	2 11/16	4 3/16	2 1/4
1 1/4"	5/8	2 11/16	4 3/16	2 1/4
1 1/2"	5/8	2 11/16	4 3/16	2 1/4


NO	Description	Material
1	Body	Brass
2	Flange End Cap	Brass
3	Union Cap	Brass
4	Seat	PTFE
5	Ball	Brass HCP
6	Stem	Brass
7	Stem Seal	PTFE
8	Packing Gland	Brass
9	Lever Handle	Steel CP
10	Handle Jacket	Vinyl
11	Handle Nut	Steel CP
12	Seat	PTFE
13	Ball	Brass HCP
14	Stem	Brass
15	Stem Seal	PTFE
16	Packing Gland	Brass
17	Handle	Aluminum
18	Handle Screw	Brass
19	End Cap	Brass
20	Washer	EPDM
21	Cap And Strap	Brass w/ EPDM Strap
22	Flange Ring	Brass
23	Flange	Brass
24	Nut	Stainless Steel
25	Bolt	Stainless Steel

Webstone VALVE INNOVATION


Quality and Commitment Since 1954


THIS SPACE FOR DESIGNER/ENGINEER APPROVAL				
Job/Customer	Date	Contractor		
Model Specified	Qty	Approved By		
Designer/Engineer	Date	Contractor's PO#		
Submitted By	Date	Other		





RIGHT FLANGE





Specifications: Designed for residential, commercial or industrial use with water or a glycol mixture in a closed loop Hydronic system. This approved Webstone valve assembly design can be used in both near boiler piping applications as well as secondary circuit loops and is actuated by blowout proof stems and feature adjustable packing glands. Threaded ends comply with ANSI B1.20.1. Solder joint temperature ratings are per ASME B16.18 Annex A for 95-5 solder. Other solder materials have lower pressure/temperature limits. Do not silver braze or overheat valves when soldering.



Quality and Commitment Since 1954