

Windex[®]

Powerized Glass Cleaner with Ammonia-D[®] (RTU)



Cleans a variety of hard surfaces without streaking or filming.

Effective

- ▶ Recommended for cleaning a variety of hard surfaces, including chrome, porcelain, ceramic tile, Plexiglas[®], Formica[®] counters, mirrors, plastic, vinyl, tabletops and glass
- ▶ No streaking or filming – a special detergent system whisks away dirt without streaking or filming, leaving glass and other surfaces sparkling clean
- ▶ Contains Ammonia-D[®] – an exclusive glass cleaning formula
- ▶ Pleasing fragrance – the clean, fresh scent of Windex[®] Glass Cleaner makes it pleasing to work with

Recommended For

- ▶ Food Service
 - ▶ Healthcare
 - ▶ Education
 - ▶ Retail
 - ▶ Lodging
-



Use Overview

Windex® Powerized Glass Cleaner with Ammonia-D® (RTU) cleans with Ammonia-D® for a streak-free shine. Loosens soil upon contact. Won't streak or leave a film. Also cleans chrome, stainless steel, Plexiglas®, mirrors, ceramic tile, enamel, plastic and other hard surfaces. Contains no phosphates.

Use Directions:

- ▶ Pump trigger to prime.
- ▶ Spray a fine mist over entire surface, spread at once and polish dry.
- ▶ For best results use paper towels or dry, lint free cloths. Change towels or cloths when dirty to avoid redepositing soil.
- ▶ Do not contaminate water, food or feed by use, storage or disposal.
- ▶ Rinsing with potable water is required if used on equipment that will be returned to a food processing area.



Note: Do not use on wood or other varnished surfaces. Not recommended for use on film tinted windows, vinyl surfaces, painted surfaces and dashboards as damage may occur. Always spot test other surfaces before using. Unplug electrical appliances before using. Suitable for use in non-food processing areas.

Product Specifications

Description	Concentrate
Color/Form	Clear blue liquid
Flash Point	185° F (85.0° C)
pH	10.7
Scent	Ammonia
Shelf Life	2 years
Solubility	Complete
Specific Gravity	0.997

Hazard Rating

HMIS	Concentrate	NFPA
0	Health	0
2	Flammability	1
0	Reactivity	0

4=Very High; 3=High; 2=Moderate; 1=Slight; 0=Insignificant.

Available Items

Product Code	Description/Package Size	Dilution
90139	12 x 32 oz. / 946 mL Trigger Sprayer	Ready-to-Use
90135	12 x 32 oz. / 946 mL Capped Trigger Sprayer	Ready-to-Use
90940	4 x 1 gal. / 3.78 L Containers	Ready-to-Use
90122	1 x 5 gal. / 18.9 L Bag-in-Box	Ready-to-Use

Safety Reminder

Please make sure your employees read and understand the product label and Material Safety Data Sheet before using this product. The label contains directions for use, and both the label and MSDS contain hazard warnings, precautionary statements and first aid procedures. MSDS are available on-line at www.diversey.com or by calling 888 352 2249.

Windex® and Ammonia-D® are registered trademarks used under authority of S.C. Johnson & Son, Inc., Racine, WI USA.

Plexiglas® is a registered trademark of Rohm & Haas Company.

Formica® is a registered trademark of The Formica Corporation.

For additional information, please contact us at +1 800 558 2332 or at www.diversey.com

© 2012 Diversey, Inc., 8310 16th Street, Sturtevant, WI 53177-1964. All Rights Reserved. SPC50200 (12/046)

