

## Air Handling Systems

# Microlite<sup>®</sup> XG<sup>™</sup>

Formaldehyde-free<sup>™</sup> Fiber Glass Duct Wrap Insulation

#### Description

Microlite XG Formaldehyde-free<sup>™</sup> duct wrap insulation is a white, lightweight, highly resilient, blanket-type thermal insulation. The insulation blanket is manufactured from rotary-process fiber glass bonded with a special thermosetting acrylic resin.

#### **Available Forms**

Microlite XG Formaldehyde-free<sup>™</sup> insulation is available in a variety of densities, thicknesses and roll lengths. It is supplied with an FSK (foil-scrim-kraft) vapor barrier facing to meet installed performance requirements, with a 2<sup>™</sup> (51 mm) stapling tab.

#### Uses

Microlite XG insulation is recommended as thermal insulation for the exterior of HVAC systems or other spaces or surfaces where temperature control is required.

#### **Facing Information**

FSK Aluminum Foil

Reinforced with fiber glass scrim laminated to UL-rated kraft. Permeance: 0.02 perms\*

\*Per ASTM E96, Procedure A for facing material prior to lamination. After lamination, permeance values may be higher.

#### **General Properties**

Temperature (max.) – ASTM C411	250°F (121°C)
Water vapor sorption – ASTM C1104	<5% by weight
Corrosivity with steel – ASTM C665	Does not accelerate
Fungi resistance – ASTM C1338	Does not breed or promote

#### **Standard Thicknesses and Packaging**

	100' Roll (31 m)	75' Roll (23 m)	50' Roll (15 m)
Туре	Thickness, ir	. ,	(1011)
75	11⁄2 (38)	2, 2 <sup>1</sup> / <sub>3</sub> (51, 58)	3 (76)
100	11⁄2 (38)	2 (51)	-
150	-	1½ (38)	2 (51)

Note: Additional thicknesses, widths and other lengths available on special order. Contact Regional Sales Office for availability.



#### **Surface Burning Characteristics**

Microlite XG insulation meets the Surface Burning Characteristics and Limited Combustibility of the following standards:

Maximum Flame Spread Index

Maximum Smoke Developed Index

25

50

Standard/Test Method

- ASTM E84
- UL 723
- NFPA 90A and 90B
- UL Guide No. 40 U8.3. Card R3711
- CAN/ULC S102-1188

Note: Faced materials are tested as composite products (insulation, adhesive and facing).

#### **Specification Compliance**

ASTM C1290	Туре 75, 100 & 150
ASTM C553* Type II	Type 75, 100 & 150
Type III	Type 150
*For faced material: 250°F (121°C) maximum ten	nperature.
ASTM C1136s <sup>†</sup>	
Туре II	FSK Facing
<sup>†</sup> Replaces HH-B-100B, Type II.	
Canada: CGSB 51-GP-11M	
NYC MEA 40-75-M	

#### **Green Building Certifications**

Recycled Content	SCS Certified
ES 1350	Meets Requirements
ENERGY STAR®	Yes
LEED <sup>®</sup> Credits	See JM.com/buildgreen,
LEED <sup>®</sup> New Construction	JM LEED <sup>®</sup> Credit Guide
	(HIG-1231)



SCIENTIFIC CERTIFICATION SYSTEMS



20% Post-consumer NTIFIC CERTIFICATION SYSTEMS

#### Certified JM Formaldehyde-free™ Fiber Glass Insulation



Certified JM Formaldehyde-free<sup>™</sup> fiber glass insulation offers superior thermal and acoustical performance—and it improves indoor air quality because it's made without formaldehyde. Why is that important? Because the U.S. Environmental Protection Agency (EPA) recommends limiting exposure to formaldehyde as much as possible, and the California Air Resources Board, a division of the California EPA, recommends that builders and architects use building materials and insulation made without formaldehyde.

# Microlite<sup>®</sup> XG<sup>™</sup>

### Formaldehyde-free<sup>™</sup> Fiber Glass Duct Wrap Insulation

#### **Application Recommendations**


The R-value will vary depending upon how much the insulation is compressed during installation. To obtain the published installed R-values, the insulation stretch-out should be determined using the following table:

#### **Duct Wrap Stretch-outs**

	Installed			
Labeled	Compressed			
Thick. (in)	Thickness (in)	Round	Square	Rectangular
1	0.75	P+ 7.0"	P+ 6.0"	P+ 5.0"
11⁄2	1.125	P+ 9.5"	P+ 8.0"	P+ 7.0"
2	1.50	P+ 12.0"	P+ 10.0"	P+ 8.0"
<b>2</b> <sup>1</sup> / <sub>3</sub>	1.75	P+ 13.0"	P+ 11.0"	P+ 8.5"
3	2.25	P+ 17.0"	P+ 14.5"	P+11.5"

Stretch-outs include 2" (51 mm) for overlap. P = perimeter of duct to be insulated.

Prepare overlap by removing approximately 2" (51 mm) of insulation from facing.



#### Thermal Conductivity (ASTM C518)

	k*		k	
	Compressed Thickness		Labeled Thickness	;
Туре	Btu•in/(hr•ft²•°F)	W/m∙°C	Btu•in/(hr•ft²•°F)	W/m∙°C
75	0.27	0.039	0.29	0.042
100	0.25	0.036	0.27	0.039
150	0.24	0.035	0.25	0.036

Conductivity at 75°F (24°C) mean temperature. \*Tested with material thickness compressed 25%. Before applying duct wrap, sheet metal duct shall be clean, dry and tightly sealed at all joints and seams.

Wrap insulation around duct with facing to the outside so the  $2^{"}$  (51 mm) flap completely overlaps facing and insulation at the other end of stretchout. Insulation shall be snugly butted.

Secure seams with outward clinching staples placed approximately 6" (152 mm) on center. If required, seal seam with pressure-sensitive tape designed for use with duct insulation. Insulation on the underside of ducts spanning 24" (610 mm) or greater shall be secured with mechanical fasteners and speed clips spaced approximately 18" (457 mm) on center. Fasteners should be cut off flush after the speed clips are installed, and when required, sealed with the same tape as specified above.

Adjacent sections of duct wrap insulation shall be snugly butted with the circumferential 2" (51 mm) tape flap overlapping and secured as recommended for the longitudinal seam. When a vapor seal is required, two coats of vapor retarder mastic reinforced with one layer of 4" (102 mm) wide, open-weave glass fabric may be used in lieu of pressuresensitive tape.

#### **Guide Specifications**

Insulation for Metal Ducts. All ducts shall be insulated on the outside with a Formaldehyde-free<sup>™</sup>, flexible glass fiber blanket. Microlite XG Formaldehyde-free<sup>™</sup> fiber glass duct wrap insulation should have a minimum installed R-value\* of \_\_\_\_\_\_, and a Type\_\_\_\_\_ facing. Insulation shall be furnished with a factory-applied facing with a composite UL FHC rating of 25/50.

\*The minimum insulation installed R-value should be determined in accordance to the duct operating and ambient conditions.

Labeled Thickness			Installed "R"**		Out-of-Package "R"	
Туре	in	mm	(hr∙ft²•°F)/Btu	m²∙°C/W	(hr∙ft²•°F)/Btu	m²•°C/W
75	11/2	38	4.2	0.74	5.2	0.92
	2	51	5.6	0.99	6.9	1.22
	<b>2</b> <sup>1</sup> / <sub>3</sub>	58	6.5	1.15	8.0	1.41
	3	76	8.3	1.46	10.3	1.81
100	1½	38	4.5	0.79	5.6	0.99
	2	51	6.0	1.06	7.4	1.30
150	1½	38	4.7	0.83	6.0	1.06
	2	51	6.3	1.11	8.0	1.41

\*\*Installed R-value calculated with a material thickness compressed to a maximum of 25% following recommended duct wrap stretch-outs.

## Insulation Systems Eastern Region P.O. Box 158 Defiance, OH 43512


Defiance, OH 43512 (800) 334-2399 Fax: (419) 784-7866

Western Region and Canada P.O. Box 5108 Denver, CO 80217 (800) 368-4431 Fax: (303) 978-4661

North American Sales Offices,

The physical and chemical properties of the Microlite® XG<sup>™</sup> Formaldehyde-free<sup>™</sup> fiber glass duct Wrap Insulation listed herein represent typical, average values obtained in accordance with accepted test methods and are subject to normal manufacturing variations. They are supplied as a technical service and are subject to change without notice. Numerical flame spread and smoke developed ratings are not intended to reflect hazards presented by these or any other materials under actual fire conditions. Check with the Regional Sales Office nearest you to ensure current information. All Johns Manville products are sold subject to Johns Manville's standard Terms and Conditions, including Limited Warranty and Limitation of Remedy. For a copy of the Johns Manville standard Terms and Conditions, Limited Warranty and Limitation of Remedy, and information on other Johns Manville thermal insulation and systems, call (800) 654-3103.

Printed on recycled paper.



Denver, CO 80202 (800) 654-3103 specJM.com

AHS-331 03/12 (Replaces 06/10)