


# SPT-100x - Pressure Switch



The World's Leading Producer of  
**Air Movement Products**  
 6393 Powers Avenue  
 Jacksonville, Florida 32217-2298  
 P: 800.961.7370 F: 800.961.7379  
 www.solerpalau-usa.com



## Specifications:

Integral recycling delay timer with 10 minute ON, 15 seconds OFF cycle, 120 volt input.

Power: 120 V AC +10%/-15%, 50/60 Hz.

Timing Range: 10 minutes (600 seconds)  $\pm$ 10%

Output: SPST NO relay rated for 8 amps (resistive) @ 250 V AC or 1/8 hp @ 250 V AC.

Electrical Connections: Terminal block with clamp-type screw connector suitable for 12-26 AWG.

Temperature Range: -40 to 140 °F (-40 to 60 °C)

ACCESSORY MODEL	1	2	3	4	5	REMARKS

PROJECT: \_\_\_\_\_ CONTRACTOR: \_\_\_\_\_  
 LOCATION: \_\_\_\_\_ REVISION DATE: \_\_\_\_\_  
 FORM NO.: \_\_\_\_\_ SUBMITTED BY: \_\_\_\_\_ DATE: \_\_\_\_\_  
 ENGINEER: \_\_\_\_\_ APPROVED BY: \_\_\_\_\_ DATE: \_\_\_\_\_

For more information contact us at [www.solerpalau-usa.com](http://www.solerpalau-usa.com) or 1.800.961.7370 for additional submittal drawings.

Soler & Palau will not be responsible for fabrication changes or errors resulting from customer use of a non-current submittal drawing.

