


| Catalog No. | Finish | | Lamping | Type | Dimensions (Inches) | | | |
|-------------|----------------|-----------------|------------|------|---------------------|---|---|---|
| | Brushed Nickel | Venetian Bronze | | | A | B | C | D |
| | | | | | | | | |
| P2745 | -09 | -74 | 4 (m) 100w | | | | | |



Specifications:

General

- Etched glass shades: 5-1/2" W., 5" ht., 1-5/8" center hole
- Square bar supports the shades
- Plated Brushed Nickel (-09) finish
- Painted Venetian Bronze (-74) finish
- Mounts in "up" or "down" position
- Steel construction
- Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, fixtures are available

Mounting

- Wall mount
- Back plate covers a standard 4" hexagonal recessed outlet box: 13-5/8", 4-3/16" ht., 1" depth
- Mounting strap for outlet box included

Electrical

- Medium base ceramic sockets
- Pre-wired

Labeling

- UL-CUL Damp location listed