


SUBMITTAL INFORMATION

Repair Clamps - (F1-xxx-length style)



6" TO 8" STAINLESS STEEL REPAIR CLAMPS WITH DUCTILE IRON LUGS



Optional Stainless Taps

ASTM A240 type 304 stainless steel TIG welded to band. Available with AWWA, or I.P. threads.

Band

ASTM A240 type 304 stainless steel

Lugs

Ductile Iron per ASTM A536
Finish: Standard Shop Coat

Nuts and Bolts

Low alloy steel per ASTM A242 and AWWA C111/A21.11

Optional


304 Stainless Steel Bolts and Nuts

Gasket

Gridded Virgin SBR compounded for water service, per ASTM D2000. Buna-N, Nitrile, is available as optional material.

Armor

ASTM A240 type 304 heavy gauge stainless steel, mold bonded into the gasket to insure uniform compression against the pipe



OUTLET THREAD TAP CODE

| CC (AWWA) THREAD | | IP THREAD | |
|------------------|-------------|-----------|----------|
| THREAD | CODE NUMBER | THREAD | CODE No. |
| 3/4" CC | -CC3 | 3/4" IP | -IP3 |
| 1" CC | -CC4 | 1" IP | -IP4 |
| 1-1/4" CC | -CC5 | 1-1/4" IP | -IP5 |
| 1-1/2" CC | -CC6 | 1-1/2" IP | -IP6 |
| 2" CC | -CC7 | 2" IP | -IP7 |

| NOM. PIPE SIZE | PIPE O.D. RANGE | LENGTH AND APPROXIMATE WEIGHT (LBS.) | | | | | | BOLT SIZE | BAND THICKNESS | CATALOG NUMBER F1-XXX-LENGTH | ✓ SUBMITTED ITEM(S) |
|-------------------|--------------------|--------------------------------------|-----|-------|-----|-----|-----|---------------|-------------------|---------------------------------|------------------------|
| | | 7.5" | 10" | 12.5" | 15" | 20" | 30" | | | | |
| 6" | 5.95 - 6.35 | 12 | 16 | 20 | 24 | 32 | 48 | 5/8" x 6-1/2" | 20 GA. | F1-635- | |
| | 6.56 - 6.96 | | | | | | | | | F1-696- | |
| | 6.84 - 7.24 | F1-724- | | | | | | | | | |
| | 7.05 - 7.45 | F1-745- | | | | | | | | | |
| 8" | 7.45 - 7.85 | 13 | 17 | 21 | 25 | 34 | 51 | | | F1-785- | |
| | 7.95 - 8.35 | | | | | | | | | F1-835- | |
| | 8.00 - 8.40 | | | | | | | | | F1-840- | |
| | 8.54 - 8.94 | | | | | | | | | F1-894- | |
| | 8.99 - 9.39 | 14 | 19 | 23 | 28 | 37 | 55 | | | F1-939- | |
| | 9.27 - 9.67 | | | | | | | | | F1-967- | |
| | 9.70 - 10.10 | | | | | | | | | F1-1010- | |
| | | | | | | | | | | | |
| Number of Bolts | | 3 | 4 | 5 | 6 | 8 | 12 | | | | |

FEATURES

- Drop-in bolt design allows bolts to remain attached - no loose parts to lose in the ditch
- Also available in two- and three- section clamps for a wider range of pipe sizes and tolerances
- Optional Outlet Taps are available for repair of service line pull-outs. Add tapping code to catalog number
- All welds are fully passivated to restore corrosion resistant characteristics of stainless steel
- Removable lugs
- UL Classified to ANSI/NSF Standard 61

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443

Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167

<http://www.fordmeterbox.com>

04/13/11

Submitted By: