



Compact Fluorescent


**Random**  
**ENERGY STAR® qualified**

**Close-To-Ceiling**

Catalog No.	Finish			Lamping	Type _____		
	Brushed Nickel	Polished Chrome	Antique Bronze		-09WB	-15WB	-20WB
P3624				2-13w GU-24 (included)	<input type="checkbox"/>		<input type="checkbox"/>
P3642				2-13w GU-24 (included)	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
P3651				2-13w GU-24 (included)			<input type="checkbox"/>
P3660				2-13w GU-24 (included)			<input type="checkbox"/>

Catalog No.	Finish	Lamping	Dimensions (Inches)	
			A	B
P3624	-09WB	2-13w GU-24 (included)	14	6-5/8
P3642	-09WB -15WB	2-13w GU-24 (included)	14	6-5/8
P3651	-20WB	2-13w GU-24 (included)	14	6-5/8
P3660	-20WB	2-13w GU-24 (included)	14	6-5/8



**Specifications:**

General

- Alabaster glass (P3624), Etched glass (P3642), Light Umber Etched glass (P3651), Etched Umber Linen glass (P3660) shade: 12-7/8" dia., 5-1/4" ht.
- Steel construction
- Plated Brushed Nickel (-09WB), Polished Chrome (-15WB) finishes
- Painted Antique Bronze (-20WB) finish
- 13w GU24 self-ballasted GU-24 lamps (included)
- ENERGY STAR® qualified
- Companion Close-to-ceiling, fixtures

Mounting

- Ceiling mount
- Ceiling pan covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- GU24 base sockets
- Pre-wired

Labeling

- cCSAus Damp location listed



Progress Lighting  
701 Millennium Blvd.  
Greenville, South Carolina  
29607

www.progresslighting.com

Rev. 08/13