
SUBMITTAL INFORMATION

Steel Tapping Sleeve - *(FTSC-xxxx-x style)*




STEEL TAPPING SLEEVE (EPOXY COATED) - 16" TO 24"


Flange - ASTM A36 Carbon Steel - Flat face, recessed for standard tapping valve.

3/4-14 No-Lead Brass Test Plug

Bolts and Nuts - Grade 18-8 type 304 stainless steel

Finish - Fusion-bonded epoxy coating no less than 12 mils thick





Gasket - Buna-N (Nitrile) ASTM D2000 BA508

Body - Heavy welded steel with a recessed groove to retain the gasket.

CLASSIFIED UL WATER QUALITY

Nom. Pipe Size	Sleeve O.D. Range	By	Flange Size Code*	Nominal Dimensions - Inches A	B	C	D	No. of Bolts	Approx. Wt. Lbs.	Sleeve Number*	✓ Submitted Item(s)
16"-18"	17.33-17.87 17.88-18.43 18.46-19.03 18.87-19.45 19.41-20.01		3	4-3/64	3-1/16	5-3/16	16	6	105	FTSC-1787- **FTSC-1843- **FTSC-1903- FTSC-1945- FTSC-2001-	
			4	5-3/64	4-1/8	5-3/16	16	6	110		
			6	7-3/64	6-1/4	5-3/16	16	6	120		
			8	9-3/64	8-1/4	5-3/16	20	8	175		
			10	11-3/64	10-1/4	5-3/16	20	10	220		
			12	13-3/64	12-1/4	5-3/16	24	12	270		
			14	15-9/32	13-1/2	6-1/4	28	14	325		
			16	17-9/32	15-1/2	6-1/4	32	16	410		
18"-20"	19.88-20.48 20.29-20.92 20.93-21.57 21.51-22.15 22.16-22.81		3	4-3/64	3-1/16	5-3/16	16	6	120	FTSC-2048- FTSC-2092- FTSC-2157- FTSC-2215- FTSC-2281-	
			4	5-3/64	4-1/8	5-3/16	16	6	120		
			6	7-3/64	6-1/4	5-3/16	16	6	125		
			8	9-3/64	8-1/4	5-3/16	20	8	180		
			10	11-3/64	10-1/4	5-3/16	20	10	230		
			12	13-3/64	12-1/4	5-3/16	24	12	290		
			14	15-9/32	13-1/2	6-1/4	28	14	-		
			16	17-9/32	15-1/2	6-1/4	32	16	500		
			18	19-1/2	17-1/2	6-1/4	36	18	-		
			20	21-1/2	19-1/2	6-1/4	40	20	-		
20"-24"	22.78-23.45 23.46-24.16 24.15-24.85 24.82-25.52		3	4-3/64	3-1/16	5-3/16	16	6	131	FTSC-2345- FTSC-2416- FTSC-2485- FTSC-2552-	
			4	5-3/64	4-1/8	5-3/16	16	6	131		
			6	7-3/64	6-1/4	5-3/16	16	6	142		
			8	9-3/64	8-1/4	5-3/16	20	8	196		
			10	11-3/64	10-1/4	5-3/16	20	10	257		
			12	13-3/64	12-1/4	5-3/16	24	12	283		
			14	15-9/32	13-1/2	6-1/4	28	14	-		
			16	17-9/32	15-1/2	6-1/4	32	16	480		
			18	19-1/2	17-1/2	6-1/4	36	18	-		
			20	21-1/2	19-1/2	6-1/4	40	20	-		
24"	25.71-26.41 26.55-27.25 27.26-27.96 28.14-28.84		3	4-3/64	3-1/16	5-3/16	16	6	147	FTSC-2641- FTSC-2725- FTSC-2796- FTSC-2884-	
			4	5-3/64	4-1/8	5-3/16	16	6	147		
			6	7-3/64	6-1/4	5-3/16	16	6	155		
			8	9-3/64	8-1/4	5-3/16	20	8	217		
			10	11-3/64	10-1/4	5-3/16	20	10	260		
			12	13-3/64	12-1/4	5-3/16	24	12	325		
			14	15-9/32	13-1/2	6-1/4	28	14	-		
			16	17-9/32	15-1/2	6-1/4	32	16	490		
			18	19-1/2	17-1/2	6-1/4	36	18	-		
			20	21-1/2	19-1/2	6-1/4	40	20	600		
			24	25-1/2	23-1/2	6-1/4	48	24	-		

***To Order**: Add Flange Size Code to the Sleeve Number. Example: A 12" Flange on 24" cast iron pipe would be FTSC-2641-12.
** Size on Size for this range is not available.
Note: A 1" undersize cutter is required for flanges 14" and larger. Oversize outlets are available by special request.

FEATURES

- Heavy welded steel meeting ASTM A36 36,000 psi minimum yield
- Bolts and nuts are made of Grade 18-8 type 304 stainless steel
- Ring style gasket is Buna-N (Nitrile) ASTM D2000 BA508
- Fusion-bonded epoxy-coating on body is no less than 12 mils thick
- UL Classified to ANSI/NSF Standard 61

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.

The Ford Meter Box Company, Inc.
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443
Phone: 260-563-3171 / Fax: 800-826-3487
Overseas Fax: 260-563-0167
http://www.fordmeterbox.com

10/08/13

Submitted By: