


Type _____

-09 -20 -20EUL

P3855 ☐ ☐ ☐

Catalog No.	Finish			Lamping	Dimensions (Inches)	
	Brushed Nickel	Antique Bronze	Antique Bronze		A	B
P3855	-09	-20	-20EUL	2 (m) 100w	13-3/8	9-5/8



Specifications:

General

- Etched (-09), Tea-stained (-20), Etched Umber Linen (-20EUL) glass cone shaped bowl: 13-3/8" dia., 5-1/8" ht.
- Plated Brushed Nickel (-09) finish
- Painted Antique Bronze (-20, -20EUL) finishes
- Steel construction
- Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available

Mounting

- Ceiling semi-flush mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- Medium base ceramic
- Pre-wired

Labeling

- cCSAus Damp location listed