

# **Devonshire® Rite-Temp®**

Pressure-balancing Bath and Shower Valve Trim
K-T395-4E

### **Features**

- Metal construction.
- Intended for use with Rite-Temp® or HiFlow Rite-Temp® valves.
- Includes showerhead with arm and flange, 5-1/4" (133 mm) diverter spout with NPT, and faceplate with handle.
- 2.0 gal/min (7.6 l/min) maximum flow rate showerhead with Katalyst<sup>®</sup> Spray Technology.

## **Required Accessories**

K- 2971-KS 3/4" Pressure-balancing Valve

or

K- 304-CS Pressure-balancing Valve With Stops

K- 304-CX Pressure-balancing Valve Less Stops

or

K- 304-K Pressure-balancing Valve Less Stops

or

K- 304-KS Pressure-balancing Valve With Stops

K- 304-PS Pressure-balancing Valve With Stops

K- 304-PX Pressure-balancing Valve Less Steps

or

K- 304-US Pressure-balancing Valve With Stops

K- 304-UX Pressure-balancing Valve Less Stops

## **Optional Accessories**

88526 Thin Wall Trim Kit





### Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 EPA WaterSense®

# **KOHLER® Faucet Lifetime Limited Warranty**

See website for detailed warranty information.

### **Available Color/Finishes**

Color tiles intended for reference only.

Color Code Description




SN Vibrant® Polished Nickel





# Devonshire® Rite-Temp®

Pressure-balancing Bath and Shower Valve Trim
K-T395-4E



Complete bath and shower faucet with Rite-Temp valve shown.

### **Technical Information**

All product dimensions are nominal.

Spout reach: 4-7/16" (113 mm)

Showerhead:

Rated maximum flow: 2 gal/min (7.6 l/min) Pressure: 80 psi (5.5 bar)

#### **Notes**

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between valve and wall-mount spout.

