

design • illuminate • enjoy

Drawing 1 - Assembly


apart 📥

72 degrees

assembly instructions

Family: Morgan | Item No. 4875





1. Find a clear area in which you can work.


2. Unpack fixture and glass from carton.

3. Carefully review instructions prior to assembly.

Vstart here

*** The construction of this fixture will be accomplished by first assembling the main body of the fixture, making all necessary electrical connections, hanging the fixture from the ceiling, and then installing the fixture shade.

Drawing 2 - Glass Installation



SAFETY WARNING: READ WIRING AND GROUNDING INSTRUCTIONS (I.S. 18) AND ANY ADDITIONAL DIRECTIONS. TURN POWER SUPPLY OFF DURING INSTALLATION. IF NEW WIRING IS REQUIRED, CONSULT A QUALIFIED ELECTRICIAN OR LOCAL AUTHORITIES FOR CODE REQUIREMENTS.

1. To assembly main body of fixture prior to hanging, first rotate arms **(A)** attached to main body **(M)**, until they are equally spaced **72** degrees apart, see - **Drawing 1** and **2**.

2. Next take Ring (R) and slip stud (D), located in the back of arms (A), throught the holes in ring (R).

3. Next thread on barrel knob **(K)** onto end of exposed stud **(D)** to secure ring to arms **(A)**.

4. Fixture is ready for installation, please following mounting instruction sheet **(IS-19)** provided. After fixture is installed please return to this section for instructions to complete assembly.


- **1.** Prior to installing the candle sleeves and shaded, attached chained crystal **(C)** to hook located directly under the loop at the top of fixture.
- 2. To install shade first slip candle sleeve with harp (2) over socket (1) see Drawing 2.
- 3. Fixture should be lamped accordingly at this time.
- 4. Align center hole in shade mount (S) with hole in the harp (H).
- 5. Thread stud (4) into hole in harp (H) approximately 1/4".
- 6. Thread barrel knob (5) onto end of exposed stud (4) and tighten to secure shade.

06.01.13



 ${\tt design} \boldsymbol{\cdot} {\tt ill} {\tt uminate} \boldsymbol{\cdot} {\tt enjoy}$

Drawing 1 - Hanging Assembly



exposed

I.S.19 hanging instructions

Vstart here

SAFETY WARNING: READ WIRING AND GROUNDING INSTRUCTIONS (I.S. 18) AND ANY ADDITIONAL DIRECTIONS. TURN POWER SUPPLY OFF DURING INSTALLATION. IF NEW WIRING IS REQUIRED, CONSULT A QUALIFIED ELECTRICIAN OR LOCAL AUTHORITIES FOR CODE REQUIREMENTS.

- **1.** Shut off electrical current before starting. If the fixture you are replacing is turned on and off by a wall switch, simply turn the switch off. If not, remove the appropriate fuse (or open the circut breakers) until the fixture is dead.
- DO NOT restore current either by fuse, breaker or switch until the new fixture is completely wired and in place.
- **1**. fasten mounting strap (1) to outlet box (A) with the two 8-32 screws (2) -see Drawing 1.
- 2. Thread 2 hex nuts (3a) and (3b) onto threaded tubing (4).
- **3**. Thread one end of threaded tubing **(4)** into loop **(5)** a minimum of 1/2" to 3/4". Thighten hexnut **(3a)** against loop **(5)** to lock loop in position.
- 4. Thread other end of threaded tube (4) into mounting strap approximately 1/2".
- 5. Slip canopy (B) over loop (5) and adjust height of loop so half of the threaded area on the loop is exposed see Drawing 2 below. After loop height is adjusted, thigten hex nut (3b) up against mounting strap, tighten against mounting strap to lock loop and threaded tube in position.
- Remove mounting strap (1) from junction box (A), and thread third hex nut (3c) onto end of threaded tube (4) above the mounting strap, tighten against mounting strap to lock assembly in position.
- 7. Remount mounting strap to junction box.
- **1.** Taking the chain, determine the length you require to hang the fixture.
- 2. Attach one end of the chain to the top loop of the fixture see Drawing 2.
- 3. Now slip loop collar (5) and canopy (B) onto chain.

4. Attach other end of chain to loop **(4)**. Get assistance for this step since fixture may be heavy and difficult to hold while attaching the chain.

1. Unwrap supply wire and ground wire and weave them up through the chain.

2. Slip supply wire and ground wire through center of loop (4).

3. Connect ground wire to mounting strap (1) using green ground screw (6).

4. Make electrical connections from supply wire to fixture lead wires. Refer to instruction sheet **(I.S. 18)** and follow all instructions to make all necessary wiring connections.

5. Slip canopy up firmly against the ceiling and secure by turning the threaded collar **(5)** on loop **(4)** until tight.



design • illuminate • enjoy

SAFETY WARNING: READ WIRING AND GROUNDING INSTRUCTIONS (I.S. 18) AND ANY ADDITIONAL DIRECTIONS. TURN POWER SUPPLY OFF DURING INSTALLATION. IF NEW WIRING IS REQUIRED, CONSULT A QUALIFIED ELECTRICIAN OR LOCAL AUTHORITIES FOR CODE REQUIREMENTS.

wiring instructions

Indoor Fixtures

1. Connect positive supply wire **(A)** (typically black or the smooth, unmarked side of the two-conductor cord) to positive fixture lead **(B)** with appropriately sized twist on connector - see **Drawings 1 or 2**.

2. Connect negative supply wire **(C)** (typically white or the ribbed, marked side of the two-conductor cord) to negative fixture lead **(D)**.

3. Please refer to the **grounding instructions** below to complete all electrical connections.

Outdoor Fixtures

1. Connect positive supply wire **(A)** (typically black or the smooth unmarked side of the two-conductor cord) to positive fixture lead **(B)** with appropriately sized twist on connector - see **Drawings 2 or 3**.

2. Connect negative supply wire **(C)** (typically white or the ribbed, marked side of the two-conductor cord) to negative fixture lead **(D)**.

3. Cover open end of connectors with silicone sealant to form a watertight seal.

• If installing a wall mount fixture, use caulk to seal gaps between the fixture mounting plate (backplate) and the wall. This will help prevent water from entering the outlet box. If the wall surface is lap siding, use caulk and a fixture mounting platform specially.

4. Please refer to the **grounding instructions** below to complete all electrical connections.

grounding instructions

Flush Mount Fixtures

For positive grounding in a 3-wire electrical system, fasten the fixture ground wire **(E)** (typically copper or green plastic coated) to the fixture mounting strap **(1)** with the ground screw **(2)** - see **Drawing 1**.


Note: On straps for screw supported fixtures, first install the two mounting screws in strap. Any remaining tapped hole may be used for the ground screw.

Chain Hung Fixtures

Loop fixture ground wire **(E)** (typically copper or green plastic coated) under the head of the ground screw **(2)** on fixture mounting strap **(1)** and connect to the loose end of the fixture ground wire directly to the ground wire of the building system with appropriately sized twist-on connectors - see **Drawing 2**.

Post-Mount Fixtures


Connect fixture ground wire **(E)** (typically copper or green plastic coated) to power supply ground with appropriately sized twist-on connector inside post. Cover open end of connector with silicone sealant to form a watertight seal - see **Drawing 3**.



Drawing 1 - Flush Mount

lixture leads

Drawing 2 - Chain Hung



Drawing 3 - Post-Mount

