

Underscore®

5' Bath **K-5713-W1**



Features

- Dual lumbar supports two-person bathing by offering comfort at both ends
- Center drain.
- Slotted overflow allows for deep soaking. Requires K-7271 or K-7272 Clearflo slotted overflow bath drain (sold separately).
- Bask® heated surface creates spa-like relaxation with soothing warmth on your back, shoulders, and neck.
- Three heat settings allow you to customize the surface temperature.

Material

Acrylic

Installation

Drop-in

Required Accessories

K- 7271 Brass Slotted Overflow Bath Drain or

K-7272 PVC Slotted Overflow Bath Drain

Recommended Accessories

K- 24916 Wireless Music Kit



Codes/Standards

CSA B45.5/IAPMO Z124 UL 1795 CSA C22.2 No. 218.2 Greenguard UL 2818 - Gold CARB P2

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Descriptio
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	G9	Sandbar







Underscore®


5' Bath **K-5713-W1**


No change in measurements if connected with drain illustrated. (K-7272)





Faucet Hole Locations (For KOHLER® Brand Only)





Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Heated Surface: 120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Installation: Drop-in Drain location: Center

Basin area, bottom: 43" x 25-5/8" (1093 mm x 651 mm)
Basin area, top: 55-9/16" x 28-3/8" (1411 mm x 720 mm)

Weight: 90 lbs (40.8 kg)

Minimum floor load: 45.4 lbs/ft² (221.7 kg/m²)

Water depth: 16-5/16" (415 mm) Water capacity: 72.017 gal (272.6 L)

Template: Drop-in, 1268438-7, required, included

Under-mount kit: 814-NA

Electrical component Heated Surface: 120 V, 1.1 A, 60 Hz, 65

rating: W

Notes

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

